


ITEM NO.	CATALOG NO.	LENGTH		
		L (IN)	L (FT)	L [mm]
332999	BB154L12	12	1.0	[305]
10065681	BB154L24	24	2.0	[610]
10068555	BB154L36	36	3.0	[914]
10109592	BB154L48	48	4.0	[1219]
10065680	BB154L60	60	5.0	[1524]
25004254	BB154L72	72	6.0	[1829]
332793	BB154L120	120	10.0	[3048]
25015481	BB154L126	126	10.5	[3200]
26001003	BB154L144	144	12.0	[3658]
33208L	BB154L240	240	20.0	[6096]
50047578	BB154L300	300	25.0	[7620]
25021386	BB154L360	360	30.0	[9144]
26000340	BB154L480	480	40.0	[12192]
081030	BB154L600	600	50.0	[15240]
33209X	BB154L840	840	70.0	[21336]
081019	BB154L1200	1200	100.0	[30480]
25020958	BB154L1380	1380	115.0	[35052]
081062	BB154L1800	1800	150.0	[45720]
332159	BB154L2400	2400	200.0	[60960]
081027	BB154L3600	3600	300.0	[91440]
33286L	BB154L6000	6000	500.0	[152400]
332150	BB154L7200	7200	600.0	[182880]
25016469	BB154L7800	7800	650.0	[198120]
002048	BB154L12000	12000	1000.0	[304800]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	09/22/2014	NEW DRAWING CREATED	37902	PB	DD



BRAID
3/0 AWG EQUIVALENT
(154 kcmil)

NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
2. MATERIAL:
TIN PLATED COPPER
3. FOR OTHER BRAID SIZES, REFERENCE DRAWING #10110676.
4. AVAILABLE IN OTHER LENGTHS UPON REQUEST.
5. LONG LENGTHS MAY NOT BE ONE CONTINUOUS PIECE.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BB154L--(TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: PARTHIBAN B 9/22/2014	
		CHECKER: L TROMBLEY 10/7/2014	
		DSN APRVL: L TROMBLEY 10/7/2014	
		MFG APRVL: --	
		QA APRVL: C LINDQUIST 10/8/2014	
		MKT APRVL: K ROBICHEAU 10/7/2014	
		PROD FAM: --	
		DRAWING NO	
		50049478	
		REV	
		A	
		SHEET 1 OF 1	