


| ITEM NO. | CATALOG NO. | LENGTH | | |
|----------|-------------|--------|--------|----------|
| | | L (IN) | L (FT) | L [mm] |
| 25019792 | BB226L120 | 120 | 10.0 | [3048] |
| 25021439 | BB226L240 | 240 | 20.0 | [6096] |
| 332960 | BB226L300 | 300 | 25.0 | [7620] |
| 25021387 | BB226L360 | 360 | 30.0 | [9144] |
| 332071 | BB226L600 | 600 | 50.0 | [15240] |
| 332184 | BB226L900 | 900 | 75.0 | [22860] |
| 332070 | BB226L1080 | 1080 | 90.0 | [27432] |
| 332423 | BB226L1200 | 1200 | 100.0 | [30480] |
| 332181 | BB226L1800 | 1800 | 150.0 | [45720] |
| 332108 | BB226L2400 | 2400 | 200.0 | [60960] |
| 002049 | BB226L6000 | 6000 | 500.0 | [152400] |
| 002050 | BB226L12000 | 12000 | 1000.0 | [304800] |

| REV | DATE | DESCRIPTION | ECO | BY | C'H.K. |
|-----|------------|---------------------|-------|----|--------|
| A | 09/22/2014 | NEW DRAWING CREATED | 37902 | PB | DD |



BRAID
4/0 AWG EQUIVALENT
(226 kcmil)

NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
2. MATERIAL:
TIN PLATED COPPER
3. FOR OTHER BRAID SIZES, REFERENCE DRAWING #10110676.
4. AVAILABLE IN OTHER LENGTHS UPON REQUEST.
5. LONG LENGTHS MAY NOT BE ONE CONTINUOUS PIECE.

| | | | |
|---|--|----------------------------------|--|
| TO ORDER BURNDY® PRODUCTS CALL | | BRAID | |
| UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) | | ITEM NO: SEE TABLE | |
| CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) | | CAT. NO: BB226L--(TABLE) | |
| FOR PRODUCT INFO: http://www.burndy.com | | DRAWN BY: PARTHIBAN B 9/22/2014 | |
| | | CHECKER: L TROMBLEY 10/7/2014 | |
| | | DSN APRVL: L TROMBLEY 10/7/2014 | |
| | | MFG APRVL: -- | |
| | | QA APRVL: C LINDQUIST 10/8/2014 | |
| | | MKT APRVL: K ROBICHEAU 10/7/2014 | |
| | | PROJ #: -- | |
| | | SIZE: B | |
| | | DRAWING NO: 50049479 | |
| | | REV: A | |
| | | SHEET 1 OF 1 | |