



CATALOG NO.	L
BD7T38	7.00"
BD8T38	8.00"
BD9T38	9.00"
BD11T38	11.00"
BD12T38	12.00"
BD12D50T38	12.50"
BD14D50T38	14.50"
BD16T38	16.00"
BD24T38	24.00"

REV	DATE	DESCRIPTION	ECO	BY	CHK.
F	09/21/2020	UPDATED PART TO TABLE	53221	JL	BE



NOTES:

- MATERIAL: BRAID: TIN PLATED COPPER
FERRULES: COPPER TUBING
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3 UL LISTED AND CSA CERTIFIED GROUNDING AND BONDING EQUIPMENT.

4 TN SUFFIX DENOTES TIN PLATED FERRULES

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

BRAID		DRAWING NO	REV
ITEM NO: SEE TABLE		50050030	F
CAT. NO: SEE TABLE			
DRAWN BY: SENTHIL	9/1/2014		
CHECKER: MANIKANDAN.B	9/1/2014		
DSN APRVL: L TROMBLEY	9/16/2014		
MFG APRVL: M STEVENS	9/17/2014		
QA APRVL: C LINDQUIST	9/21/2014		
MKT APRVL: K ROBICHEAU	9/15/2014		
PROD FAM: MECHANICAL GROUNDING	SIZE		
PROJECT #: FPN1809016			
DOCUMENT TYPE: SALES			
REL LEVEL: Released			

