



CATALOG NUMBER	ITEM NUMBER	L1	L2
BD18D5G285TN	50050393	18.50 [470]	17.75 [451]
BD20D5G285TN	50050394	20.50 [521]	19.75 [502]
BD25D5G285TN	50050395	25.5 [648]	24.75 [629]
BD26D5G285TN	50050396	26.50 [673]	25.75 [654]
BD28D5G285TN	50050397	28.50 [724]	27.75 [705]
BD30D28G285TN	50088440	30.28 [769]	29.53 [750]
BD32D25G285TN	50050398	32.25 [819]	31.50 [800]
BD45G285TN	50050399	45.00 [1143]	44.25 [1124]
BD52G285TN	50050400	52.00 [1321]	51.25 [1302]
BD56G285TN	50050401	56.00 [1422]	55.25 [1403]
BD58D75G285TN	50050402	58.75 [1492]	58.00 [1473]
BD71D75G285TN	50050403	71.75 [1822]	71.00 [1803]
BD79D49G285TN	50088441	79.49 [2019]	78.74 [2000]
BD119G285TN	50050404	119.00 [3023]	118.25 [3004]
BD126D75G285TN	50050405	126.75 [3219]	126.00 [3200]
BD133D75G285TN	50050406	133.75 [3397]	133.00 [3378]

REV	DATE	DESCRIPTION	ECO	BY	C'H.K.
B	20/12/2017	UPDATED AS PER REQUEST	48253	YR	VS



NOTES:

- APPROXIMATE AMP RATING: 190A INDOOR, 250A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
 - DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS, FILE E9999.
- 4 ALL SIZES ARE CERTIFIED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BD-G285TN (TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: AUGUSTIN 09/08/2014	
		CHECKER: T LOGAN 09/12/2014	
		DSN APRVL: T LOGAN 09/12/2014	
		MFG APRVL: S MATTHEW 09/12/2014	
		QA APRVL: L CARL 09/12/2014	
		MKT APRVL: R KATHLEEN 09/15/2014	
		PROD FAM: MECHANICAL GROUNDING	DRAWING NO
		PROJECT #: --	SIZE
		DOCUMENT TYPE: SALES	50050407
		REL LEVEL: Released	B
			SHEET 1 OF 1
			REV
			B