





FLAME RETARDANT COVER CAT. NO	COPPER CONDUCTOR SIZES (FLEX)		TOOLING(* NUMBER OF CRIMPS)							DIE INDEX AND EMBOSSMENT
	MAIN	TAP 1	Y35, Y39	*	Y750	*	Y46 	*	COLOR CODE	
CF11FR	8-12 (8-12)	8-12 (8-12)	U240	1	U240	1	U240	1	RED	240

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	10/06/2014	NEW DRAWING CREATED	38009	TS	BSB



**NOTES:**

1. MATERIAL: COPPER
2. FINISH: TIN PLATE.
3. ACCOMODATES CLASS B, C, D, G, H, I AND DLO CONDUCTOR TYPES.
4. RECOMMENDED CONDUCTOR STRIP LENGTH (CONNECTOR LENGTH + 1/8" MAX).  
CONNECTOR LENGTH SHOWN BY DIMENSION "L".
5.  USE PUADP1 ADAPTOR WITH U-DIES IN THE Y46.
6. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		"C" SHAPE COPPER TAP	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 142019	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: YCHC8TC8	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: T.SATHISH 10/06/2014	
		CHECKER: R.ROMAN 10/20/2014	
		DSN APRVL: R.ROMAN 10/20/2014	
		MFG APRVL: --	
		QA APRVL: T.WATTS 10/20/2014	
		MKT APRVL: K.BOUTIN 10/20/2014	
		PROD FAM: --	
		DRAWING NO	
		50051297	
		REV	
		A	
		SHEET 1 OF 1	