


CAT. NO.	ITEN NUMBER	" L"
BF6T716	50049994	6.00"
BF8T716	50097610	8.00"
BF10T716	50097611	10.00"
BF12T716	50047794	12.00"
BF18T716	50047795	18.00"

REV	DATE	DESCRIPTION	ECO	BY	CHK.
C	01/18/2019	ADDED DATA TO TABLE	50685	JL	BE



NOTES:

- APPROXIMATE AMP. RATING: 360 INDOOR, 430 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- ALL SIZES ARE LISTED TO CSA C22.2 NO. 41 GROUNDING & BONDING EQUIPMENT STANDARDS.
- FOR TIN PLATED FERRULES, ADD SUFFIX -TN TO CAT NO.

TO ORDER BURNDY PRODUCTS CALL		BRAID, FLEXIBLE	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BF-T716 (TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: N.D.KANNAN 11/24/2014	
		CHECKER: L.TROMBLEY 12/17/2014	
		DSN APRVL: L.TROMBLEY 12/17/2014	
		MFG APRVL: M.STEVENS 12/16/2014	
		QA APRVL: C.LINDQUIST 12/21/2014	
		MKT APRVL: K.ROBICHEAU 12/16/2014	
PROD FAM: --	DRAWING NO	REV	
PROJECT #: --	SIZE	50053106	C
DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
REL LEVEL: Released			