



BRAID		
ITEM NO	CAT NO	L
50066294	B4E12G88TN	12.00
50066295	B4E18G88TN	18.00

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	12/2/2015	CREATE SALES DRAWING	42333	GHR	



NOTES:

1. APPROXIMATE AMP RATING: 850A INDOOR, 1020A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
3. ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

<p>TO ORDER BURNDY® PRODUCTS CALL</p> <p>UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)</p> <p>CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)</p> <p>FOR PRODUCT INFO: http://www.burndy.com</p>	BRAID		
	ITEM NO: SEE TABLE		
	CAT. NO: SEE TABLE		
	DRAWN BY: G.RUGGIERO	12/2/2015	
	CHECKER: --		
	DSN APRVL: L.TROMBLEY	12/8/2015	
	MFG APRVL: M.STEVENSON	12/3/2015	
	QA APRVL: C.LINDQUIST	12/4/2015	
	MKT APRVL: K.ROBICHEAU	12/3/2015	
	PROD FAM: MECHANICAL GROUNDING	DRAWING NO	REV
PROJECT #: --	SIZE		
DOCUMENT TYPE: SALES	50066296	A	
REL LEVEL: Released	B	SHEET 1 OF 1	