


REV	DATE	DESCRIPTION	ECO	BY	C'HK.
A	01/19/2016	FOCUS REQUEST PIN FPN1512022	42367	AV	MB



**NOTES:**

1. APPROXIMATE AMP RATING: 1000 INDOOR, 1200 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
3. ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
4. APPROXIMATE WEIGHT : 22.474 LBS.
5. HEAT SHRINK FACTORY INSTALLED

TO ORDER BURNDY® PRODUCTS CALL		FLEXIBLE BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 50066377	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: B4F90T12TNB	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: AVINASH V 19-01-2016	
		CHECKER: MANIKANDAN B 19-01-2016	
		DSN APRVL: --	
		MFG APRVL: --	
		QA APRVL: --	
		MKT APRVL: --	
		PROD FAM: MECHANICAL GROUNDING	
		DRAWING NO	
		50066378	
		REV	
		A	
		SHEET 1 OF 1	