


REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	05/02/2065	FOCUS REQUEST FPN1601051	42691	AV	MB



NOTES:

1. APPROXIMATE AMP RATING: 93A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3 ALL SIZE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- 4 ALL SIZE LISTED TO CSA 22.2 NO. 41 GROUNDING & BONDING EQUIPMENT STANDARDS.
- 5 APPROXIMATE WEIGHT : .657 LBS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES		ITEM NO: 50067381	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: BD12T58	
CANADA:		DRAWN BY: AVINASH V 2/5/2016	
1-800-361-6975 (QUEBEC)		CHECKER: MANIKANDAN B 2/5/2016	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: --	
FOR PRODUCT INFO: http://www.burndy.com		MFG APRVL: --	
		QA APRVL: --	
		MKT APRVL: --	
PROD FAM: MECHANICAL GROUNDING	DRAWING NO	REV	
PROJECT #: FPN1601051	SIZE	50068179	A
DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
REL LEVEL: Released			