



ITEM NO.	CATALOG NO.	ACCOMMODATES $\triangleleft 2$		INSTALLATION TOOLING		
		RUN	TAP	DIE INDEX	DIE NO.	NO OF CRIMPS
50069805	NYFTH4634CCP	1500 kcmil (1.412 DIA.) CABLE	500 kcmil (.814 DIA.) CABLE	20	U34RT	2
50069807	NYFTH4628CCP		4/0 STR. (.528 DIA.) CABLE	15	U28RT	4

REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	04/13/2016	NEW DRAWING RELEASED	43227	SV	MB



SECTION A-A



NOTES:

1. MATERIAL : AS NOTED.
2. ACCOMMODATES: SEE TABLE
3. ALL METAL PARTS TIN PLATED.
4. ALL SEAMS AND JOINTS IN INSULATION TO BE TAPED BY CUSTOMER AFTER INSTALLATION.
5. MAXIMUM VOLTAGE RATING: 600 VOLTS.
6. THIS DRAWING TO BE INTERPRETED PER ASME Y14.5.
7. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		HIGH CAPACITY LIMITER TEE CONNECTOR	
UNITED STATES		ITEM NO: SEE TABLE	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: SEE TABLE	
CANADA:		DRAWN BY: SENTHIL 04/13/2016	
1-800-361-6975 (QUEBEC)		CHECKER: MANIKANDAN 04/13/2016	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: D BOUDREAU 04/19/2016	
FOR PRODUCT INFO: http://www.burndy.com		MFG APRVL: J HEAD 04/26/2016	
		QA APRVL: T WATTS 04/19/2016	
		MKT APRVL: --	
		PROD FAM: --	
		PROJECT #: --	
		DOCUMENT TYPE: SALES	
		REL LEVEL: Released	
		DRAWING NO	
		50069808	
		REV	
		A	
		SHEET 1 OF 1	

