



CATALOG NUMBER	ITEM NUMBER	LENGTH mm [IN]
WILEYBRAID6-12	50070183	152.4 [6.0]
WILEYBRAID8-12	50070184	203.2 [8.0]
WILEYBRAID10-12	50070185	254 [10.0]
WILEYBRAID12-12	50068085	304.8 [12.0]
WILEYBRAID18-12	50067320	457.2 [18.0]
WILEYBRAID24-12	50066980	609.6 [24.0]
WILEYBRAID30-12	50067325	762 [30.0]
WILEYBRAID36-12	50067330	914.4 [36.0]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	30/14/2018	OBSOLETE INDIVIDUAL SALES DRAWINGS OF WILEYBRAIDXX-12 SERIES.	48705	TM	EM



3D VIEW

NOTES:

- MATERIAL: TIN PLATED COPPER BRAID (#6 AWG)
FERRULE: TIN PLATED COPPER
- DIMENSIONS IN BRACKETS [] ARE IN INCHES ROUNDED OFF TO THE NEAREST TENTH, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- UL LISTED TO UL467 STANDARD FOR GROUNDING AND BONDING DEVICES.
ETL LISTED TO UL2703 STANDARD FOR PV GROUND LUGS AND BONDING JUMPERS.

TO ORDER BURNDY PRODUCTS CALL		BRAID	
UNITED STATES		ITEM NO: SEE TABLE	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: WILEYBRAID-- SEE TABLE	
CANADA:		DRAWN BY: S.MOORTHY 30-03-2016	
1-800-361-6975 (QUEBEC)		CHECKER: E.MARTIN 02-04-2018	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: E.MARTIN 02-04-2018	
FOR PRODUCT INFO: http://www.burndy.com		MFG APRVL: --	
		QA APRVL: B.POST 02-04-2018	
		MKT APRVL: S.PARSONS 06-04-2018	
PROD FAM: WILEY	DRAWING NO	REV	
PROJECT #: SALES	50070212	B	
REL LEVEL: Released	B		
	SHEET 1 OF 1		