




REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	10/19/2016	RELEASE SALES DRAWING	45163	GHR	



NOTES:

1. APPROXIMATE AMP RATING: 380 AMP INDOOR, 455 AMP OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
3. ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com		ITEM NO: 50072064	
		CAT. NO: B2D36TNG89	
DRAWN BY: SENTHIL 5/25/2016		DRAWING NO	
CHECKER: B.MANIKANDAN 5/24/2016		REV	
DSN APRVL: L.TROMBLEY 10/24/2016		50072065	
MFG APRVL: M.STEVENS 10/21/2016		A	
QA APRVL: C.LINDQUIST 10/24/2016		SHEET 1 OF 1	
MKT APRVL: K.ROBICHEAU 10/24/2016			
PROD FAM: MECHANICAL GROUNDING	SIZE		
PROJECT #: FPN1604096	B		
DOCUMENT TYPE: SALES			
REL LEVEL: Released			