


REV	DATE	DESCRIPTION	ECO	BY	C'H.K.
A	04/27/2017	FOCUS REQUEST FPN1607040	46607	CV	MB



- NOTES:
- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
  - ALL SIZE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENTS STANDARDS.
  - ALL SIZE LISTED TO CSA 22.2 NO. 41 GROUNDING & BONDING EQUIPMENTS STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 50074265	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BB100L12D81M16TN	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: VIMAL C 7/25/2016	
		CHECKER: MANIKANDAN B 7/25/2016	
		DSN APRVL: H.GOMEZ 5/2/2017	
		MFG APRVL: --	
		QA APRVL: E.VARGAS 5/2/2017	
		MKT APRVL: K.ROBICHEAU 5/2/2017	
PROD FAM: MECHANICAL GROUNDING	DRAWING NO	REV	
PROJECT #: FPN1607040	SIZE	50074266	A
DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
REL LEVEL: Released			