


S.NO	ITEM NUMBER	CATALOG NUMBER <sup>5</sup>	L
1	50078948	BD12N2U	12 [305]
2	33205R	BD14N2U	14 [356]
3	50131877	BD15N2U	15 [381]
4	50078949	BD18N2U	18 [457]
5	50078950	BD24N2U	24 [610]
6	50078951	BD36N2U	36 [914]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
D	02/03/2023	ADD 14" AND 15" LENGTHS TO TABLE	230120027198	PC	NB



**NOTES:**

1. APPROXIMATE AMP RATING: 190 INDOOR, 225 OUTDOOR CURRENTS PROVIDED ARE BASED ON A 30°C RISE OVER AMBIENT TEMPERATURE THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
3. ALL SIZES ARE LISTED TO GROUNDING & BONDING EQUIPMENT STANDARDS.
4. BRAID SIZE MAY BE DESIGNATED BY SUFFIXES REPRESENTING VARIATIONS IN LENGTH, QUANTITY & SIZE OF MOUNTING HOLES, PAD SIZE AND FINISH. (REF. NOTES <sup>3</sup>)
5. ADD "TN" SUFFIX FOR TIN-PLATED FERRULES.

TO ORDER BURNDY® PRODUCTS CALL  UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)  CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)  FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>	<b>BRAID</b>	
	ITEM NO: -- CAT. NO: BD--N2U (SEE TABLE)	
DRAWN BY: T.SATHISH 12/19/2016 CHECKER: L.TROMBLEY 1/23/2017 DSN APRVL: L.TROMBLEY 1/23/2017 MFG APRVL: M.STEVENS 1/17/2017 QA APRVL: C.LINDQUIST 1/26/2017 MKT APRVL: K.ROBICHEAU 2/5/2017	PROJ FAM: -- PROJECT #: -- DOCUMENT TYPE: SALES REL LEVEL: Released	DRAWING NO <b>50078953</b> SIZE <b>B</b> REV <b>D</b> SHEET 1 OF 1