


BURNDY® ITEM NUMBER	BURNDY® CATALOG NUMBER	MAXIMUM BUNDLE DIA. IN [MM]	MATERIAL	MOUNTING SCREW	COLOR	WIDTH IN [MM] ± .01 [1]	HOLE LOCATION IN [MM] ± .04 [1]	PACKAGE QTY.	CARTON QTY.
10023760	CH2C	.13 [3]	NYLON 6/6	#8 SCREW	NATURAL	.38 [10]	.31 [8]	100	1000
10023762	CH2M	.13 [3]	NYLON 6/6	#8 SCREW	NATURAL	.38 [10]	.31 [8]	1000	1000
10023764	CH3C	.21 [5]	NYLON 6/6	#8 SCREW	NATURAL	.38 [10]	.36 [9]	100	1000
10023765	CH3C0	.21 [5]	NYLON 6/6	#8 SCREW	BLACK	.38 [10]	.36 [9]	100	1000
10023766	CH3M	.21 [5]	NYLON 6/6	#8 SCREW	NATURAL	.38 [10]	.36 [9]	1000	1000
10023768	CH4C	.27 [7]	NYLON 6/6	#8 SCREW	NATURAL	.40 [10]	.41 [10]	100	1000
10023769	CH4C0	.27 [7]	NYLON 6/6	#8 SCREW	BLACK	.40 [10]	.41 [10]	100	1000
10023770	CH4M	.27 [7]	NYLON 6/6	#8 SCREW	NATURAL	.40 [10]	.41 [10]	1000	1000
10023771	CH4M0	.27 [7]	NYLON 6/6	#8 SCREW	BLACK	.40 [10]	.41 [10]	1000	1000
10023772	CH5C	.33 [8]	NYLON 6/6	#8 SCREW	NATURAL	.39 [10]	.44 [11]	100	1000
10023773	CH5C0	.33 [8]	NYLON 6/6	#8 SCREW	BLACK	.39 [10]	.44 [11]	100	1000
10023774	CH5M	.33 [8]	NYLON 6/6	#8 SCREW	NATURAL	.39 [10]	.44 [11]	1000	1000
10023776	CH6C	.43 [11]	NYLON 6/6	#8 SCREW	NATURAL	.47 [12]	.49 [12]	100	1000
10023777	CH6C0	.43 [11]	NYLON 6/6	#8 SCREW	BLACK	.47 [12]	.49 [12]	100	1000
10023778	CH6M	.43 [11]	NYLON 6/6	#8 SCREW	NATURAL	.47 [12]	.49 [12]	1000	1000
10023779	CH6M0	.43 [11]	NYLON 6/6	#8 SCREW	BLACK	.47 [12]	.49 [12]	1000	1000
10023784	CH8C	.54 [14]	NYLON 6/6	#8 SCREW	NATURAL	.48 [12]	.58 [15]	100	1000
10023785	CH8C0	.54 [14]	NYLON 6/6	#8 SCREW	BLACK	.48 [12]	.58 [15]	100	1000
10023786	CH8M	.54 [14]	NYLON 6/6	#8 SCREW	NATURAL	.48 [12]	.58 [15]	1000	1000
10023796	CH11C	.69 [17]	NYLON 6/6	#8 SCREW	NATURAL	.49 [12]	.62 [16]	100	1000
10023798	CH11M	.69 [17]	NYLON 6/6	#8 SCREW	NATURAL	.49 [12]	.62 [16]	1000	1000
10023800	CH12C	.78 [20]	NYLON 6/6	#8 SCREW	NATURAL	.46 [12]	.71 [18]	100	1000
10023801	CH12C0	.78 [20]	NYLON 6/6	#8 SCREW	BLACK	.46 [12]	.71 [18]	100	1000
10023802	CH12M	.78 [20]	NYLON 6/6	#8 SCREW	NATURAL	.46 [12]	.71 [18]	1000	1000
10023803	CH12M0	.78 [20]	NYLON 6/6	#8 SCREW	BLACK	.46 [12]	.71 [18]	1000	1000
10023812	CH16C	1.07 [27]	NYLON 6/6	#8 SCREW	NATURAL	.47 [12]	.83 [21]	100	1000
10023814	CH16M	1.07 [27]	NYLON 6/6	#8 SCREW	NATURAL	.47 [12]	.83 [21]	1000	1000
10023816	CH18C	1.33 [34]	NYLON 6/6	#8 SCREW	NATURAL	.47 [12]	1.02 [26]	100	1000
10023818	CH18M	1.33 [34]	NYLON 6/6	#8 SCREW	NATURAL	.47 [12]	1.02 [26]	1000	1000
10023820	CH24L	1.65 [42]	NYLON 6/6	#8 SCREW	NATURAL	.49 [12]	1.09 [28]	50	1000
10023822	CH24C	1.65 [42]	NYLON 6/6	#8 SCREW	NATURAL	.49 [12]	1.09 [28]	100	1000
10023823	CH24C0	1.65 [42]	NYLON 6/6	#8 SCREW	BLACK	.49 [12]	1.09 [28]	100	1000

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	06/05/2017	BAG DIMENSIONS REMOVED.	46429	DD	NJS



NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

2. ELONGATED MOUNTING SCREW HOLE AT BOTTOM SIDE AS ILLUSTRATED.

TO ORDER BURNDY PRODUCTS CALL		CABLE HANGERS	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: D.DHEENA 3/6/2017	
		CHECKER: K.BOUTIN 3/22/2017	
		DSN APRVL: A.MONTMINY 3/22/2017	
		MFG APRVL: []	
		QA APRVL: B.POST 3/21/2017	
		MKT APRVL: K.BOUTIN 3/22/2017	
		PROJ #:	
		SIZE	
		50080809	
		B	
		SHEET 1 OF 1	
		REV	
		B	