


ITEM NUMBER	CATALOG NUMBER	TENSILE STRENGTH LB / N	MATERIAL	COLOR	FEATURE	BUNDLE DIA. MIN. IN [MM]	BUNDLE DIA. MAX. IN [MM]	L IN [MM]	W IN [MM]	MIN. INSTALL TEMP. °F / °C	MIN. OPER. TEMP. °F / °C	MAX. OPER. TEMP. °F / °C	PKG. QTY.	CARTON QTY.	REV	DATE	DESCRIPTION	ECO	BY	CHK
															A	03/02/2018	NEW DRAWING CREATION	48604	DD	PB
10023464	CT120300L	120 / 534	NYLON 6/6	NATURAL	STANDARD	.18 [4.8]	3.00 [76.2]	11.42 [290]	.30 [7.6]	32 / 0	-40 / -40	185 / 85	50	2000						
10023506	CT120300L0	120 / 534	NYLON 6/6	UV BLACK	STANDARD	.18 [4.8]	3.00 [76.2]	11.42 [290]	.30 [7.6]	32 / 0	-40 / -40	185 / 85	50	2000						



NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY PRODUCTS CALL		UNIRAP™	
UNITED STATES		ITEM NO: SEE TABLE	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: SEE TABLE	
CANADA:		DRAWN BY: D.DHEENA 03/02/2018	
1-800-361-6975 (QUEBEC)		CHECKER: K.BOUTIN 03/16/2018	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: K.CASTONGUAY 03/20/2018	
FOR PRODUCT INFO: http://www.burndy.com		MFG APRVL: J.VERRANAULT 03/16/2018	
		QA APRVL: B.POST 03/15/2018	
		MKT APRVL: K.BOUTIN 03/16/2018	
PROD FAM:	DRAWING NO	REV	
PROJECT #:	50090186	A	
DOCUMENT TYPE: SALES	SIZE		
REL LEVEL: Released	B		
	SHEET 1 OF 1		