



REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	04/08/2020	NICKEL PLATING NOTES ADDED	53334	WP	SS

WIRE SIZE (AWG)	CATALOG NUMBER	BULK CATALOG NUMBER	L MAX.	O.D. MAX	WIRE STRIP LENGTH ± .03 [± .8]	INSTALLATION TOOLING
22-18 Str. and Sol.	YSV18BOX	YSV18	.66 [16.6]	.14 [3.6]	9/32" [7.1]	Y1022, Y8MRB1, Y81KFT, Y81KFTMBH, PAT81KFT18V, MRE1022B, Y122CMR (Wire range is No. 14-10 stranded or solid when crimped with the Y122CMR.)
20-14 Str. and Sol.	YSV14BOX	YSV14	.67 [17.0]	.17 [4.3]		
12-10 Str. and Sol.	YSV10BOX	YSV10	.78 [19.9]	.22 [5.6]	5/16" [7.9]	



NOTES:

1. TERMINAL: TIN PLATED COPPER
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS AND ARE FOR REFERENCE ONLY.
3. UL LISTED & CSA CERTIFIED SPLICING WIRE CONNECTORS PER UL486C (FILE E9498) & CSA C22.2 NO.188 REQUIREMENTS (FILE 42862)
4. DISCONTINUED TOOLS: PATMD1022LI
CONTACT TECH SERVICE FOR INFORMATION ABOUT APPROVED APPLICATIONS (1-800-451-4956)
5. ADD "NK" SUFFIX FOR NICKEL PLATED HYLINK.

TO ORDER BURNDY® PRODUCTS CALL		HYLINK™ (MULT.)	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: TYPE YSV	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: RBABU 12/06/2018	
		CHECKER: V.SAKTHIVEL 12/06/2018	
		DSN APRVL: K.CASTONGUAY 12/18/2018	
		MFG APRVL: --	
		QA APRVL: B.POST 12/18/2018	
		MKT APRVL: M.BAILLY 12/18/2018	
		PROD FAM: --	
		PROJECT #: --	
		SIZE	
		D	
		DOCUMENT TYPE: SALES	
		REL LEVEL: Released	
		DRAWING NO	
		50094197	
		SHEET 1 OF 1	
		REV	
		C	