




REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	2/22/2019	NEW DRAWING CREATION	50931	PP	WP

WIRE SIZE (AWG)	CATALOG NUMBER	NEMA Tab Size	LENGTH (L)	WIDTH (W)	WIRE STRIP LENGTH ±.03 [±.8]	COLOR CODE	INSTALLATION TOOLING (ONE CRIMP)
22-18 Str. and Sol.	FQP18F11X03D*	.11 X .02	.79 [20.1]	.11 [2.8]	3/8" [9.5]	RED	MRE1022NV, Y1022, Y10D
	FQP18F18X02D	.19 X .02	.80 [20.3]	.19 [4.7]			
	FQP18F18X03D*	.19 X .03	.79 [20.1]				
	FQP18F25X03D	.25 X .03	.90 [22.9]	.25 [6.4]			
16-14 Str. and Sol.	FQP14F11X03D*	.11 X .02	.79 [20.1]	.11 [2.8]		BLUE	
	FQP14F18X02D	.19 X .02	.80 [20.3]	.19 [4.7]			
	FQP14F25X03D		.90 [22.9]				
12-10 Str. and Sol.	FQP10F25X03D	.25 X .03	.97 [24.6]	.25 [6.4]	YELLOW		



NOTES:

1. TERMINAL: TIN PLATED BRASS
2. INSULATION: POLYVINYLCHLORIDE
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS AND ARE FOR REFERENCE ONLY.
4. CONNECTORS ARE cULus LISTED FOR USE IN CANADA AND THE U.S.
5. WIRE CONNECTOR:
 - 300V MAXIMUM
 - TEMPERATURE RATING OF INSULATING MATERIAL 75°C
 - FLAME RATING: UL94 V-0
6. ITEMS WITH CATALOG NUMBERS FOLLOWED BY ASTERISKS (*) ARE NOT cULus LISTED.

TO ORDER BURNDY® PRODUCTS CALL		FINGRIP	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: TYPE FQP-F	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: P.PRASANTH 2/22/2019 CHECKER: P.WINSON 2/22/2019 DSN APRVL: K.CASTONGUAY 3/18/2019 MFG APRVL: -- QA APRVL: B.ELLIOTT 3/18/2019 MKT APRVL: M.BAILLY 3/16/2019	
PROJ #:		SIZE	DRAWING NO
DOCUMENT TYPE: SALES		D	50094208
REL LEVEL: Released			SHEET 1 OF 1
			REV A