




REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	02/15/2019	NEW DRAWING CREATION	50831	YR	VS

WIRE SIZE (AWG)	CATALOG NUMBER (100/bag)	CATALOG NUMBER (20/bag)	NEMA Tab Size	LENGTH (L)	WIDTH (W)	WIRE STRIP LENGTH $\pm .03$ [$\pm .8$]	COLOR CODE	INSTALLATION TOOLING (ONE CRIMP)
22-18 Str. and Sol.	YHSQ18M25X03	YHSQ18M25X03RK	.25 X .03	1.46 [37.1]	.25 [6.4]	5/16" [7.9]	RED	MR22
16-14 Str. and Sol.	YHSQ14M25X03	YHSQ14M25X03RK	.25 X .03				BLUE	
12-10 Str. and Sol.	YHSQ10M25X03	YHSQ10M25X03RK	.25 X .03				YELLOW	



NOTES:

1. TERMINAL: TIN PLATED COPPER
2. INSULATION: HEAT SHRINK
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS AND ARE FOR REFERENCE ONLY.
4. WIRE CONNECTOR:
 MINIMUM SHRINK TEMPERATURE: 135°C
 OPERATING TEMPERATURE RANGE: -55°C TO 110°C

TO ORDER BURNDY® PRODUCTS CALL		HYDENT	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: TYPE YHSQ-M	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: R.YOGARAJ 02/15/2019	
		CHECKER: S.VENKATESAN 02/15/2019	
		DSN APRVL: --	
		MFG APRVL: --	
		QA APRVL: --	
		MKT APRVL: --	
		PROD FAM: --	
		PROJECT #: --	
		SIZE	
		D	
		DRAWING NO	
		50094213	
		REV	
		A	
		SHEET 1 OF 1	