

G SERIES INDOOR WITH TERMINAL (5/8 kV)						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	CONDUCTOR SIZE	TERMINAL CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSGI5810T1	50103401	1/0	YA252N	0.57-0.90 [14.5-23]	1.1 [28]	3
CSGI5820T1	50103402	2/0	YA262N			
CSGI5830T1	50103403	3/0	YA272N			
CSGI5840T1	50103404	4/0	YA282N			
CSGI5840T2	50103405	4/0	YA282N	0.71-1.26 [18-32]	1.5 [38]	3
CSGI58250T2	50103406	250	YA292N			
CSGI58350T2	50103407	350	YA312N			
CSGI58500T2	50103408	500	YA342N			
CSGI58350T3	50103409	350	YA312N	0.83-1.34 [21-34]	1.65 [42]	3
CSGI58400T3	50103410	400	YA322N			
CSGI58500T3	50103411	500	YA342N			
CSGI58600T3	50103412	600	YA362N			
CSGI58750T3	50103413	750	YA392N	1.04-1.54 [26.5-39]	1.97 [50]	3
CSGI58750T4	50103414	750	YA392N			
CSGI58800T4	50103415	800	YA402N			
CSGI581000T4	50103416	1000	YA442N			
CSGI581000T5	50103417	1000	YA442N	1.34-2.19 [34-55.5]	2.67 [68]	3
CSGI581250T5	50103418	1250	YA452N			
CSGI581300T5	50103419	1300	YA4532N			
CSGI581500T5	50103420	1500	YA462N			
CSGI581750T5	50103421	1750	YA472N			
CSGI582000T5	50103422	2000	YA482N			

G SERIES INDOOR WITH TERMINAL (15 kV)						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	CONDUCTOR SIZE	TERMINAL CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSGI152T1	50103423	#2	YA2C2N	0.57-0.90 [14.5-23]	1.1 [28]	3
CSGI151T1	50103424	#1	YA1C2N			
CSGI1510T1	50103425	1/0	YA252N			
CSGI1510T2	50103426	1/0	YA252N	0.71-1.26 [18-32]	1.5 [38]	3
CSGI1520T2	50103427	2/0	YA262N			
CSGI1530T2	50103428	3/0	YA272N			
CSGI1540T2	50103429	4/0	YA282N			
CSGI15250T2	50103430	250	YA292N	0.83-1.34 [21-34]	1.65 [42]	3
CSGI1540T3	50103431	4/0	YA282N			
CSGI15250T3	50103432	250	YA292N			
CSGI15300T3	50103433	300	YA302N			
CSGI15350T3	50103434	350	YA312N			
CSGI15400T3	50103435	400	YA322N			
CSGI15450T3	50103436	450	YA332N	1.04-1.54 [26.5-39]	1.97 [50]	3
CSGI15500T3	50103437	500	YA342N			
CSGI15350T4	50103438	350	YA312N			
CSGI15400T4	50103439	400	YA322N			
CSGI15450T4	50103440	450	YA332N			
CSGI15500T4	50103441	500	YA342N			
CSGI15550T4	50103442	550	YA352N	1.34-2.19 [34-55.5]	2.67 [68]	3
CSGI15600T4	50103443	600	YA362N			
CSGI15650T4	50103444	650	YA372N			
CSGI15700T4	50103445	700	YA382N			
CSGI15750T4	50103446	750	YA392N			
CSGI15750T5	50103447	750	YA392N			
CSGI15800T5	50103448	800	YA402N	1.34-2.19 [34-55.5]	2.67 [68]	3
CSGI15850T5	50103449	850	YA412N			
CSGI151000T5	50103450	1000	YA442N			
CSGI151250T5	50103451	1250	YA452N			
CSGI151300T5	50103452	1300	YA4532N			
CSGI151500T5	50103453	1500	YA462N			
CSGI151750T5	50103454	1750	YA472N	1.34-2.19 [34-55.5]	2.67 [68]	3
CSGI152000T5	50103455	2000	YA482N			

G SERIES INDOOR WITH TERMINAL (25/28 kV)						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	CONDUCTOR SIZE	TERMINAL CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSGI25281T1	50103456	1	YA1C2N	0.71-1.26 [18-32]	1.5 [38]	3
CSGI252810T1	50103457	1/0	YA252N			
CSGI252820T1	50103458	2/0	YA262N			
CSGI252830T1	50103459	3/0	YA272N			
CSGI252840T1	50103460	4/0	YA282N	0.83-1.34 [21-34]	1.65 [42]	3
CSGI252810T2	50103461	1/0	YA252N			
CSGI252820T2	50103462	2/0	YA262N			
CSGI252830T2	50103463	3/0	YA272N			
CSGI252840T2	50103464	4/0	YA282N			
CSGI2528250T2	50103465	250	YA292N			
CSGI2528250T3	50103466	250	YA292N	1.04-1.54 [26.5-39]	1.97 [50]	3
CSGI2528300T3	50103467	300	YA302N			
CSGI2528350T3	50103468	350	YA312N			
CSGI2528400T3	50103469	400	YA322N			
CSGI2528450T3	50103471	450	YA332N			
CSGI2528500T3	50103472	500	YA342N			
CSGI2528500T4	50103473	500	YA342N	1.34-2.19 [34-55.5]	2.67 [68]	3
CSGI2528550T4	50103474	550	YA352N			
CSGI2528600T4	50103475	600	YA362N			
CSGI2528650T4	50103476	650	YA372N			
CSGI2528700T4	50103477	700	YA382N			
CSGI2528750T4	50103478	750	YA392N			
CSGI2528800T4	50103479	800	YA402N			
CSGI2528850T4	50103480	850	YA412N			
CSGI25281000T4	50103481	1000	YA442N			
CSGI25281250T4	50103482	1250	YA452N			
CSGI25281300T4	50103483	1300	YA4532N			
CSGI25281500T4	50103484	1500	YA462N			

NOTES:

1. MATERIAL: SILICON RUBBER

2. KIT INCLUDES : (COLD SHRINK TERMINATION SUB ASSEMBLY, CTSR ENDSEAL TERMINATION, EXTERNAL GROUND KIT, BRAID W/O SEALANT, INSTALLATION GUIDE, VIOLET PVC TAPE).

3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.

4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.

5. CONFORMS TO ISO/IEC 17025 STANDARDS.

6. RUS APPROVED.

7. REPORT # K-423192-RC-0000-R00.



REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	01/02/2020	UPDATED TABLE DATA	52667	JL	KC

TO ORDER BURNDY® PRODUCTS CALL	COLD SHRINK G SERIES INDOOR WITH TERMINAL		
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)	ITEM NO: SEE TABLE		
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)	CAT. NO: SEE TABLE		
FOR PRODUCT INFO: http://www.burndy.com	DRAWN BY: R.BABU 11/22/2018	CHECKER: K.JAYAVIGNESH 8/29/2019	
	DSN APRVL: K.CASTONGUAY 10/11/2019	MFG APRVL:	
	QA APRVL: B.ELLIOTT 10/11/2019	MKT APRVL: K.BOUTIN 10/11/2019	
	PROD FAM:	DRAWING NO	
	PROJECT #:	SIZE	50095756
	DOCUMENT TYPE: Sales	REL LEVEL: Released	B
			SHEET 1 OF 1