

BARE CONCENTRIC NEUTRAL 15 KV					
BURNDY SLEEVE CATALOG NUMBER <sup>2</sup>	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSB15102	50104075	2	0.51-0.64 [13-16.2]	0.91 [23]	3
CSB1511210	50104076	2- 1/0	0.64-0.79 [16.2-20.2]	1.10 [28]	
CSB151220250	50104079	2/0 - 250	0.79-1.04 [20-26.4 ]	1.42 [36]	
CSB1513350500	50104083	350 - 500	1.02-1.45 [26-36.8 ]	1.77 [45]	
CSB15147501000	50104087	750 - 1000	1.34-1.77 [34-45]	2.28 [58]	


NOTES:

- MATERIAL: SILICON RUBBER
- INCLUDES : ( JOINT, SEALANT PACK, SEALANT PACK, CONSTANT FORCE SPRING, PRODUCT INSTALLATION GUIDE, VIOLET PVC TAPE).
- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.
- CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.
- CONFORMS TO ISO/IEC 17025 STANDARDS.
- RUS APPROVED.
- REPORT # HVS CST 181207.



TO ORDER BURNDY® PRODUCTS CALL		CSJ 10 SPLICE																									
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE																									
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE																									
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		<table border="1"> <tr> <td>DRAWN BY: R.BABU</td> <td>11/22/2018</td> </tr> <tr> <td>CHECKER: K.JAYAVIGNESH</td> <td>8/30/2019</td> </tr> <tr> <td>DSN APRVL: K.CASTONGUAY</td> <td>10/11/2019</td> </tr> <tr> <td>MFG APRVL:</td> <td></td> </tr> <tr> <td>QA APRVL: B.ELLIOTT</td> <td>10/11/2019</td> </tr> <tr> <td>MKT APRVL: K.BOUTIN</td> <td>10/11/2019</td> </tr> </table>		DRAWN BY: R.BABU	11/22/2018	CHECKER: K.JAYAVIGNESH	8/30/2019	DSN APRVL: K.CASTONGUAY	10/11/2019	MFG APRVL:		QA APRVL: B.ELLIOTT	10/11/2019	MKT APRVL: K.BOUTIN	10/11/2019												
DRAWN BY: R.BABU	11/22/2018																										
CHECKER: K.JAYAVIGNESH	8/30/2019																										
DSN APRVL: K.CASTONGUAY	10/11/2019																										
MFG APRVL:																											
QA APRVL: B.ELLIOTT	10/11/2019																										
MKT APRVL: K.BOUTIN	10/11/2019																										
<table border="1"> <tr> <th>REV</th> <th>DATE</th> <th>DESCRIPTION</th> <th>ECO</th> <th>BY</th> <th>C'H'K.</th> </tr> <tr> <td>C</td> <td>01/27/2020</td> <td>UPDATED AS PER MARKUP</td> <td>52903</td> <td>SS</td> <td>YR</td> </tr> </table>		REV	DATE	DESCRIPTION	ECO	BY	C'H'K.	C	01/27/2020	UPDATED AS PER MARKUP	52903	SS	YR	<table border="1"> <tr> <td>PROD FAM:</td> <td>DRAWING NO</td> <td>REV</td> </tr> <tr> <td>PROJECT #:</td> <td>SIZE</td> <td>50095757</td> </tr> <tr> <td>DOCUMENT TYPE: Sales</td> <td>B</td> <td>C</td> </tr> <tr> <td>REL LEVEL: Released</td> <td></td> <td>SHEET 1 OF 2</td> </tr> </table>		PROD FAM:	DRAWING NO	REV	PROJECT #:	SIZE	50095757	DOCUMENT TYPE: Sales	B	C	REL LEVEL: Released		SHEET 1 OF 2
REV	DATE	DESCRIPTION	ECO	BY	C'H'K.																						
C	01/27/2020	UPDATED AS PER MARKUP	52903	SS	YR																						
PROD FAM:	DRAWING NO	REV																									
PROJECT #:	SIZE	50095757																									
DOCUMENT TYPE: Sales	B	C																									
REL LEVEL: Released		SHEET 1 OF 2																									




JACKETED CONCENTRIC NEUTRAL 15 KV					
BURNDY SLEEVE CATALOG NUMBER 	BURNDY SLEEVE ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSJ15102	50104091	2	0.51-0.64 [13-16.2]	0.91 [23]	3
CSJ1511210	50104092	2 - 1/0	0.64-0.79 [16.2-20.2]	1.10 [28]	
CSJ151220250	50104095	2/0 - 250	0.79-1.04 [20-26.4 ]	1.42 [36]	
CSJ1513350500	50104099	350 - 500	1.02-1.45 [26-36.8 ]	1.77 [45]	
CSJ15147501000	50104135	750 - 1000	1.34-1.77 [34-45]	2.28 [58]	



NOTES:

1. MATERIAL: SILICON RUBBER

 INCLUDES : (JACKET, JOINT, SEALANT PACK, SEALANT PACK, CONSTANT FORCE SPRING, PRODUCT INSTALLATION GUIDE, VIOLET PVC TAPE).

3. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.


4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.

5. CONFORMS TO ISO/IEC 17025 STANDARDS.

6. RUS APPROVED.

7. REPORT # HVS CST 181207.

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	01/27/2020	UPDATED AS PER MARKUP	52903	SS	YR

TO ORDER BURNDY® PRODUCTS CALL		CSJ 10 SPLICE													
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE													
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE													
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		<table border="1"> <tr> <td>DRAWN BY: R. BABU</td> <td>11/22/2018</td> </tr> <tr> <td>CHECKER: K. JAYAVIGNESH</td> <td>8/30/2019</td> </tr> <tr> <td>DSN APRVL: K. CASTONGUAY</td> <td>10/11/2019</td> </tr> <tr> <td>MFG APRVL:</td> <td></td> </tr> <tr> <td>QA APRVL: B. ELLIOTT</td> <td>10/11/2019</td> </tr> <tr> <td>MKT APRVL: K. BOUTIN</td> <td>10/11/2019</td> </tr> </table>		DRAWN BY: R. BABU	11/22/2018	CHECKER: K. JAYAVIGNESH	8/30/2019	DSN APRVL: K. CASTONGUAY	10/11/2019	MFG APRVL:		QA APRVL: B. ELLIOTT	10/11/2019	MKT APRVL: K. BOUTIN	10/11/2019
DRAWN BY: R. BABU	11/22/2018														
CHECKER: K. JAYAVIGNESH	8/30/2019														
DSN APRVL: K. CASTONGUAY	10/11/2019														
MFG APRVL:															
QA APRVL: B. ELLIOTT	10/11/2019														
MKT APRVL: K. BOUTIN	10/11/2019														
<table border="1"> <tr> <td>PROJ #:</td> <td>SIZE</td> <td>DRAWING NO</td> <td>REV</td> </tr> <tr> <td>50095757</td> <td>B</td> <td>50095757</td> <td>C</td> </tr> </table>		PROJ #:	SIZE	DRAWING NO	REV	50095757	B	50095757	C						
PROJ #:	SIZE	DRAWING NO	REV												
50095757	B	50095757	C												
<table border="1"> <tr> <td>DOCUMENT TYPE: Sales</td> <td>REL LEVEL: Released</td> </tr> </table>		DOCUMENT TYPE: Sales	REL LEVEL: Released	SHEET 2 OF 2											
DOCUMENT TYPE: Sales	REL LEVEL: Released														