

G SERIES INDOOR WITH PIN 5/8 KV						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	CONDUCTOR SIZE	PIN CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSGI5810P1	50104349	1/0	YE25R25	0.57-0.90 [14.5-23]	1.10 [28]	3
CSGI5820P1	50104350	2/0	YE26R60			
CSGI5830P1	50104351	3/0	YE27R60			
CSGI5840P1	50104352	4/0	YE28R60			
CSGI5840P2	50104353	4/0	YE28R60	0.71-1.26 [18-32]	1.50 [38]	
CSGI58250P2	50104354	250	YE30R60			
CSGI58350P2	50104355	350	YE32R60			
CSGI58500P2	50104356	500	YE361R60			
CSGI58350P3	50104357	350	YE32R60	0.83-1.34 [21-34]	1.65 [42]	
CSGI58400P3	50104358	400	YE361R60			
CSGI58500P3	50104359	500	YE361R60			
CSGI58600P3	50104360	600	YE39R60			
CSGI58750P3	50104361	750	--	1.04-1.54 [26.5-39]	1.97 [50]	
CSGI58750P4	50104362	750	--			
CSGI58800P4	50104363	800	--			
CSGI581000P4	50104364	1000	--			
CSGI581000P5	50104365	1000	--	1.34-2.19 [34-55.5]	2.67 [68]	
CSGI581250P5	50104366	1250	--			
CSGI581300P5	50104367	1300	--			
CSGI581500P5	50104368	1500	--			
CSGI581750P5	50104369	1750	--			
CSGI582000P5	50104370	2000	--			

G SERIES INDOOR WITH PIN 15 KV						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	CONDUCTOR SIZE	PIN CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSGI152P1	50104371	#2	YE2R25	0.57-0.90 [14.5-23]	1.10 [28]	3
CSGI151P1	50104372	#1	YE2R25			
CSGI1510P1	50104373	1/0	YE25R25			
CSGI1510P2	50104374	1/0	YE25R25			
CSGI1520P2	50104375	2/0	YE26R60	0.71-1.26 [18-32]	1.50 [38]	
CSGI1530P2	50104376	3/0	YE27R60			
CSGI1540P2	50104377	4/0	YE28R60			
CSGI15250P2	50104378	250	YE30R60			
CSGI1540P3	50104379	4/0	YE28R60	0.83-1.34 [21-34]	1.65 [42]	
CSGI15250P3	50104380	250	YE30R60			
CSGI15300P3	50104381	300	YE30R60			
CSGI15350P3	50104382	350	YE32R60			
CSGI15400P3	50104383	400	YE32R60	1.04-1.54 [26.5-39]	1.97 [50]	
CSGI15450P3	50104384	450	YE361R60			
CSGI15500P3	50104385	500	YE361R60			
CSGI15350P4	50104386	350	YE32R60			
CSGI15400P4	50104387	400	YE32R60	1.34-2.19 [34-55.5]	2.67 [68]	
CSGI15450P4	50104388	450	YE361R60			
CSGI15500P4	50104389	500	YE361R60			
CSGI15550P4	50104390	550	YE39R60			
CSGI15600P4	50104391	600	YE39R60			
CSGI15650P4	50104392	650	--			
CSGI15700P4	50104393	700	--	1.34-2.19 [34-55.5]	2.67 [68]	
CSGI15750P4	50104394	750	--			
CSGI15750P5	50104395	750	--			
CSGI15800P5	50104396	800	--			
CSGI15850P5	50104397	850	--	1.34-2.19 [34-55.5]	2.67 [68]	
CSGI151000P5	50104398	1000	--			
CSGI151250P5	50104399	1250	--			
CSGI151300P5	50104400	1300	--			
CSGI151500P5	50104401	1500	--			
CSGI151750P5	50104402	1750	--			
CSGI152000P5	50104403	2000	--			

G SERIES INDOOR WITH PIN 25/28 KV						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	CONDUCTOR SIZE	PIN CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSGI25281P1	50104404	1	YE2R25	0.71-1.26 [18-32]	1.50 [38]	3
CSGI252810P1	50104405	1/0	YE25R25			
CSGI252820P1	50104406	2/0	YE26R60			
CSGI252830P1	50104407	3/0	YE27R60			
CSGI252840P1	50104408	4/0	YE28R60	0.83-1.34 [21-34]	1.65 [42]	
CSGI252810P2	50104409	1/0	YE25R25			
CSGI252820P2	50104410	2/0	YE26R60			
CSGI252830P2	50104411	3/0	YE27R60			
CSGI252840P2	50104412	4/0	YE28R60	1.04-1.54 [26.5-39]	1.97 [50]	
CSGI2528250P2	50104413	250	YE30R60			
CSGI2528250P3	50104414	250	YE30R60			
CSGI2528300P3	50104415	300	YE30R60			
CSGI2528350P3	50104416	350	YE32R60	1.34-2.19 [34-55.5]	2.67 [68]	
CSGI2528400P3	50104417	400	YE32R60			
CSGI2528450P3	50104418	450	YE361R60			
CSGI2528500P3	50104419	500	YE361R60			
CSGI2528500P4	50104420	500	YE361R60	1.34-2.19 [34-55.5]	2.67 [68]	
CSGI2528550P4	50104421	550	YE39R60			
CSGI2528600P4	50104422	600	YE39R60			
CSGI2528650P4	50104423	650	--			
CSGI2528700P4	50104424	700	--			
CSGI2528750P4	50104425	750	--			
CSGI2528800P4	50104426	800	--			
CSGI2528850P4	50104427	850	--			
CSGI25281000P4	50104428	1000	--			
CSGI25281250P4	50104429	1250	--			
CSGI25281300P4	50104430	1300	--			
CSGI25281500P4	50104431	1500	--			

NOTES:

1. MATERIAL: SILICON RUBBER

2. KIT INCLUDES: (COLD SHRINK TERMINATION SUB ASSEMBLY, CTSR ENDSEAL TERMINATION, EXTERNAL GROUND KIT, BRAID W/O SEALANT, INSTALLATION GUIDE, VIOLET PVC TAPE).

3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.

4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.

5. CONFORMS TO ISO/IEC 17025 STANDARDS.

6. RUS APPROVED.

7. REPORT # K-423192-RC-0000-R00.



REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	01/02/2020	UPDATED TABLE DATA	52667	JL	KC

TO ORDER BURNDY® PRODUCTS CALL		COLD SHRINK G SERIES INDOOR WITH PIN			
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE			
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE			
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: R.BABU 11/22/2018			
		CHECKER: K.JAYAVIGNESH 8/29/2019			
		DSN APRVL: K.CASTONGUAY 10/11/2019			
		MFG APRVL: [blank]			
		QA APRVL: B.ELLIOTT 10/11/2019			
		MKT APRVL: K.BOUTIN 10/11/2019			
		PROJ #:		DRAWING NO	
		SIZE		REV	
		B		50095760	
		REL LEVEL: Released		B	
				SHEET 1 OF 1	