

G SERIES OUTDOOR WITH PIN 5/8KV						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	SLEEVE RANGE	PIN CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSGO5810P1	50103306	1/0	YE25R25	0.57-0.90 [14.5-23]	1.10 [28]	3
CSGO5820P1	50103307	2/0	YE26R60			
CSGO5830P1	50103308	3/0	YE27R60			
CSGO5840P1	50103309	4/0	YE28R60			
CSGO5840P2	50103322	4/0	YE28R60	0.71-1.26 [18-32]	1.50 [38]	
CSGO58250P2	50103323	250	YE30R60			
CSGO58350P2	50103324	350	YE32R60			
CSGO58500P2	50103325	500	YE361R60			
CSGO58350P3	50103326	350	YE32R60	0.83-1.34 [21-34]	1.65 [42]	
CSGO58400P3	50103327	400	YE361R60			
CSGO58500P3	50103328	500	YE361R60			
CSGO58600P3	50103329	600	YE39R60			
CSGO58750P3	50103330	750	--			
CSGO58750P4	50103331	750	--	1.04-1.54 [26.5-39]	1.97 [50]	
CSGO58800P4	50103332	800	--			
CSGO581000P4	50103333	1000	--			
CSGO581000P5	50103334	1000	--			
CSGO581250P5	50103335	1250	--	1.34-2.19 [34-55.5]	2.67 [68]	
CSGO581300P5	50103336	1300	--			
CSGO581500P5	50103337	1500	--			
CSGO581750P5	50103338	1750	--			
CSGO582000P5	50103339	2000	--			

G SERIES OUTDOOR WITH PIN 15KV						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	SLEEVE RANGE	PIN CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSGO152P1	50103340	#2	YE2R25	0.57-0.90 [14.5-23]	1.10 [28]	3
CSGO151P1	50103341	1	YE2R25			
CSGO1510P1	50103342	1/0	YE25R25			
CSGO1510P2	50103343	1/0	YE25R25	0.71-1.26 [18-32]	1.50 [38]	
CSGO1520P2	50103344	2/0	YE26R60			
CSGO1530P2	50103345	3/0	YE27R60			
CSGO1540P2	50103346	4/0	YE28R60			
CSGO15250P2	50103347	250	YE30R60	0.83-1.34 [21-34]	1.65 [42]	
CSGO1540P3	50103348	4/0	YE28R60			
CSGO15250P3	50103349	250	YE30R60			
CSGO15300P3	50103350	300	YE30R60			
CSGO15350P3	50103351	350	YE32R60			
CSGO15400P3	50103352	400	YE32R60	1.04-1.54 [26.5-39]	1.97 [50]	
CSGO15450P3	50103353	450	YE361R60			
CSGO15500P3	50103354	500	YE361R60			
CSGO15350P4	50103355	350	YE32R60			
CSGO15400P4	50103356	400	YE32R60	1.04-1.54 [26.5-39]	1.97 [50]	
CSGO15450P4	50103357	450	YE361R60			
CSGO15500P4	50103358	500	YE361R60			
CSGO15550P4	50103359	550	YE39R60			
CSGO15600P4	50103360	600	YE39R60			
CSGO15650P4	50103361	650	--	1.04-1.54 [26.5-39]	1.97 [50]	
CSGO15700P4	50103362	700	--			
CSGO15750P4	50103363	750	--			
CSGO15750P5	50103364	750	--			
CSGO15800P5	50103365	800	--	1.34-2.19 [34-55.5]	2.67 [68]	
CSGO15850P5	50103366	850	--			
CSGO151000P5	50103367	1000	--			
CSGO151250P5	50103368	1250	--			
CSGO151300P5	50103369	1300	--			
CSGO151500P5	50103370	1500	--	1.34-2.19 [34-55.5]	2.67 [68]	
CSGO151750P5	50103371	1750	--			
CSGO152000P5	50103372	2000	--			

G SERIES OUTDOOR WITH PIN 25/28KV						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	SLEEVE RANGE	PIN CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSGO25281P1	50103373	1	YE2R25	0.71-1.26 [18-32]	1.50 [38]	
CSGO252810P1	50103374	1/0	YE25R25			
CSGO252820P1	50103375	2/0	YE26R60			
CSGO252830P1	50103376	3/0	YE27R60			
CSGO252840P1	50103377	4/0	YE28R60			
CSGO252810P2	50103378	1/0	YE25R25	0.83-1.34 [21-34]	1.65 [42]	
CSGO252820P2	50103379	2/0	YE26R60			
CSGO252830P2	50103380	3/0	YE27R60			
CSGO252840P2	50103381	4/0	YE28R60			
CSGO2528250P2	50103382	250	YE30R60	1.04-1.54 [26.5-39]	1.97 [50]	3
CSGO2528250P3	50103383	250	YE30R60			
CSGO2528300P3	50103384	300	YE30R60			
CSGO2528350P3	50103385	350	YE32R60			
CSGO2528400P3	50103386	400	YE32R60			
CSGO2528450P3	50103387	450	YE361R60	1.04-1.54 [26.5-39]	1.97 [50]	
CSGO2528500P3	50103388	500	YE361R60			
CSGO2528500P4	50103389	500	YE361R60			
CSGO2528550P4	50103390	550	YE39R60			
CSGO2528600P4	50103391	600	YE39R60	1.34-2.19 [34-55.5]	2.67 [68]	
CSGO2528650P4	50103392	650	--			
CSGO2528700P4	50103393	700	--			
CSGO2528750P4	50103394	750	--			
CSGO2528800P4	50103395	800	--			
CSGO2528850P4	50103396	850	--			
CSGO25281000P4	50103397	1000	--			
CSGO25281250P4	50103398	1250	--			
CSGO25281300P4	50103399	1300	--			
CSGO25281500P4	50103400	1500	--			

NOTES:

1. MATERIAL: SILICON RUBBER

2. KIT INCLUDES; (COLD SHRINK TERMINATION SUB ASSEMBLY,CTSR ENDSEAL TERMINATION, EXTERNAL GROUND KIT, BRAID W/O SEALANT,INSTALLATION GUIDE,VIOLET PVC TAPE).

3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.

4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.

5. CONFORMS TO ISO/IEC 17025 STANDARDS.

6. RUS APPROVED.

7. REPORT # K-423192-RC-0000-R00.



REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	01/27/2020	UPDATED AS PER MARKUP	52903	SS	JV

TO ORDER BURNDY® PRODUCTS CALL		COLD SHRINK G SERIES OUTDOOR WITH PIN	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: R. BABU 11/22/2018	
		CHECKER: K. JAYAVIGNESH 8/30/2019	
		DSN APRVL: K. CASTONGUAY 10/11/2019	
		MFG APRVL: [Signature]	
		QA APRVL: B. ELLIOTT 10/11/2019	
		MKT APRVL: K. BOUTIN 10/11/2019	
		PROJ FAM: [Blank]	
		DRAWING NO: 50095761	
		REV: C	
		SHEET 1 OF 1	