

| G SERIES OUTDOOR WITH TERMINAL 5/8 kV | | | | | | |
|---------------------------------------|------------------------|--------------|-------------------------|---------------------------|---------------------------------|---------------------------|
| BURNDY KIT CATALOG NUMBER | BURNDY KIT ITEM NUMBER | SLEEVE RANGE | TERMINAL CATALOG NUMBER | INSULATION DIAMETER RANGE | INSULATION DIAMETER (PRESHRINK) | STANDARD PACKAGE QUANTITY |
| CSGO5810T1 | 50103485 | 1/0 | YA252N | 0.57-0.90 [14.5-23] | 1.10 [28] | 3 |
| CSGO5820T1 | 50103486 | 2/0 | YA262N | | | |
| CSGO5830T1 | 50103487 | 3/0 | YA272N | | | |
| CSGO5840T1 | 50103488 | 4/0 | YA282N | | | |
| CSGO5840T2 | 50103489 | 4/0 | YA282N | 0.71-1.26 [18-32] | 1.50 [38] | |
| CSGO58250T2 | 50103490 | 250 | YA292N | | | |
| CSGO58350T2 | 50103491 | 350 | YA312N | | | |
| CSGO58500T2 | 50103492 | 500 | YA342N | | | |
| CSGO58350T3 | 50103493 | 350 | YA312N | 0.83-1.34 [21-34] | 1.65 [42] | |
| CSGO58400T3 | 50103494 | 400 | YA322N | | | |
| CSGO58500T3 | 50103495 | 500 | YA342N | | | |
| CSGO58600T3 | 50103496 | 600 | YA362N | | | |
| CSGO58750T3 | 50103497 | 750 | YA392N | | | |
| CSGO58750T4 | 50103498 | 750 | YA392N | 1.04-1.54 [26.5-39] | 1.97 [50] | |
| CSGO58800T4 | 50103499 | 800 | YA402N | | | |
| CSGO581000T4 | 50103500 | 1000 | YA442N | | | |
| CSGO581000T5 | 50103501 | 1000 | YA442N | 1.34-2.19 [34-55.5] | 2.67 [68] | |
| CSGO581250T5 | 50103502 | 1250 | YA452N | | | |
| CSGO581300T5 | 50103508 | 1300 | YA4532N | | | |
| CSGO581500T5 | 50103509 | 1500 | YA462N | | | |
| CSGO581750T5 | 50103510 | 1750 | YA472N | | | |
| CSGO582000T5 | 50103511 | 2000 | YA482N | | | |

| G SERIES OUTDOOR WITH TERMINAL 15 kV | | | | | | |
|--------------------------------------|------------------------|--------------|-------------------------|---------------------------|---------------------------------|---------------------------|
| BURNDY KIT CATALOG NUMBER | BURNDY KIT ITEM NUMBER | SLEEVE RANGE | TERMINAL CATALOG NUMBER | INSULATION DIAMETER RANGE | INSULATION DIAMETER (PRESHRINK) | STANDARD PACKAGE QUANTITY |
| CSGO152T1 | 50103512 | 2 | YA2C2N | 0.57-0.90 [14.5-23] | 1.10 [28] | 3 |
| CSGO151T1 | 50103513 | 1 | YA1C2N | | | |
| CSGO1510T1 | 50103514 | 1/0 | YA252N | | | |
| CSGO1510T2 | 50103515 | 1/0 | YA252N | 0.71-1.26 [18-32] | 1.50 [38] | |
| CSGO1520T2 | 50103516 | 2/0 | YA262N | | | |
| CSGO1530T2 | 50103517 | 3/0 | YA272N | | | |
| CSGO1540T2 | 50103518 | 4/0 | YA282N | | | |
| CSGO15250T2 | 50103519 | 250 | YA292N | 0.83-1.34 [21-34] | 1.65 [42] | |
| CSGO1540T3 | 50103520 | 4/0 | YA282N | | | |
| CSGO15250T3 | 50103521 | 250 | YA292N | | | |
| CSGO15300T3 | 50103522 | 300 | YA302N | | | |
| CSGO15350T3 | 50103523 | 350 | YA312N | | | |
| CSGO15400T3 | 50103524 | 400 | YA322N | | | |
| CSGO15450T3 | 50103525 | 450 | YA332N | | | |
| CSGO15500T3 | 50103526 | 500 | YA342N | 1.04-1.54 [26.5-39] | 1.97 [50] | |
| CSGO15350T4 | 50103527 | 350 | YA312N | | | |
| CSGO15400T4 | 50103528 | 400 | YA322N | | | |
| CSGO15450T4 | 50103529 | 450 | YA332N | | | |
| CSGO15500T4 | 50103530 | 500 | YA342N | | | |
| CSGO15550T4 | 50103531 | 550 | YA352N | | | |
| CSGO15600T4 | 50103532 | 600 | YA362N | | | |
| CSGO15650T4 | 50103533 | 650 | YA372N | | | |
| CSGO15700T4 | 50103534 | 700 | YA382N | 1.34-2.19 [34-55.5] | 2.67 [68] | |
| CSGO15750T4 | 50103535 | 750 | YA392N | | | |
| CSGO15750T5 | 50103536 | 750 | YA392N | | | |
| CSGO15800T5 | 50103537 | 800 | YA402N | | | |
| CSGO15850T5 | 50103538 | 850 | YA412N | | | |
| CSGO151000T5 | 50103539 | 1000 | YA442N | | | |
| CSGO151250T5 | 50103540 | 1250 | YA452N | | | |
| CSGO151300T5 | 50103541 | 1300 | YA4532N | | | |
| CSGO151500T5 | 50103542 | 1500 | YA462N | | | |
| CSGO151750T5 | 50103543 | 1750 | YA472N | | | |
| CSGO152000T5 | 50103544 | 2000 | YA482N | | | |

NOTES:

1. MATERIAL: SILICON RUBBER

2. KIT INCLUDES: (COLD SHRINK TERMINATION SUB ASSEMBLY, CTSR ENDSEAL TERMINATION, EXTERNAL GROUND KIT, BRAID W/O SEALANT, INSTALLATION GUIDE, VIOLET PVC TAPE).

3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.

4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.

5. CONFORMS TO ISO/IEC 17025 STANDARDS.


6. RUS APPROVED.

7. REPORT # K-423192-RC-0000-R00.



| REV | DATE | DESCRIPTION | ECO | BY | C'H'K. |
|-----|------------|-----------------------|-------|----|--------|
| C | 01/27/2020 | UPDATED AS PER MARKUP | 52903 | SS | YR |

| | | | |
|---|--|---------------------------------------|--------------|
| TO ORDER BURNDY® PRODUCTS CALL | | COLD SHRINK G SERIES OUTDOOR TERMINAL | |
| UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) | | ITEM NO: SEE TABLE | |
| CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) | | CAT. NO: SEE TABLE | |
| FOR PRODUCT INFO: http://www.burndy.com | | DRAWN BY: R. BABU 12/13/2018 | |
| | | CHECKER: K. JAYAVIGNESH 9/4/2019 | |
| | | DSN APRVL: K. CASTONGUAY 10/11/2019 | |
| | | MFG APRVL: [] | |
| | | QA APRVL: B. ELLIOTT 10/11/2019 | |
| | | MKT APRVL: K. BOUTIN 10/11/2019 | |
| | | PROJ #: | SIZE |
| | | 50095763 | B |
| | | RELEV: Released | SHEET 1 OF 2 |

| G SERIES OUTDOOR WITH TERMINAL 25/28 kV | | | | | | |
|---|------------------------|--------------|-------------------------|---------------------------|---------------------------------|---------------------------|
| BURNDY KIT CATALOG NUMBER  | BURNDY KIT ITEM NUMBER | SLEEVE RANGE | TERMINAL CATALOG NUMBER | INSULATION DIAMETER RANGE | INSULATION DIAMETER (PRESHRINK) | STANDARD PACKAGE QUANTITY |
| CSGO25281T1 | 50103545 | 1 | YA1C2N | 0.71-1.26 [18-32] | 1.50 [38] | 3 |
| CSGO252810T1 | 50103546 | 1/0 | YA252N | | | |
| CSGO252820T1 | 50103547 | 2/0 | YA262N | | | |
| CSGO252830T1 | 50103548 | 3/0 | YA272N | | | |
| CSGO252840T1 | 50103549 | 4/0 | YA282N | | | |
| CSGO252810T2 | 50103550 | 1/0 | YA252N | 0.83-1.34 [21-34] | 1.65 [42] | |
| CSGO252820T2 | 50103551 | 2/0 | YA262N | | | |
| CSGO252830T2 | 50103552 | 3/0 | YA272N | | | |
| CSGO252840T2 | 50103553 | 4/0 | YA282N | | | |
| CSGO2528250T2 | 50103554 | 250 | YA292N | | | |
| CSGO2528250T3 | 50103555 | 250 | YA292N | 1.04-1.54 [26.5-39] | 1.97 [50] | |
| CSGO2528300T3 | 50103556 | 300 | YA302N | | | |
| CSGO2528350T3 | 50103557 | 350 | YA312N | | | |
| CSGO2528400T3 | 50103558 | 400 | YA322N | | | |
| CSGO2528450T3 | 50103559 | 450 | YA332N | | | |
| CSGO2528500T3 | 50103560 | 500 | YA342N | | | |
| CSGO2528500T4 | 50103561 | 500 | YA342N | 1.34-2.19 [34-55.5] | 2.67 [68] | |
| CSGO2528550T4 | 50103562 | 550 | YA352N | | | |
| CSGO2528600T4 | 50103563 | 600 | YA362N | | | |
| CSGO2528650T4 | 50103564 | 650 | YA372N | | | |
| CSGO2528700T4 | 50103565 | 700 | YA382N | | | |
| CSGO2528750T4 | 50103566 | 750 | YA392N | | | |
| CSGO2528800T4 | 50103567 | 800 | YA402N | | | |
| CSGO2528850T4 | 50103568 | 850 | YA412N | | | |
| CSGO25281000T4 | 50103569 | 1000 | YA442N | | | |
| CSGO25281250T4 | 50103570 | 1250 | YA452N | | | |
| CSGO25281300T4 | 50103571 | 1300 | YA4532N | | | |
| CSGO25281500T4 | 50103572 | 1500 | YA462N | | | |



NOTES:

1. MATERIAL: SILICON RUBBER

KIT INCLUDES: (COLD SHRINK TERMINATION SUB ASSEMBLY,CTSR ENDSEAL TERMINATION,EXTERNAL GROUND KIT, BRAID W/O SEALANT, INSTALLATION GUIDE ,VIOLET PVC TAPE).

3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.


4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.

5. CONFORMS TO ISO/IEC 17025 STANDARDS.

6. RUS APPROVED.

7. REPORT # K-423192-RC-0000-R00.

| REV | DATE | DESCRIPTION | ECO | BY | C'H'K. |
|-----|------------|-----------------------|-------|----|--------|
| C | 01/27/2020 | UPDATED AS PER MARKUP | 52903 | SS | YR |

| | | | | | | | | | | | | | | | |
|--|------------|--|------------|------------------|------------|------------------------|----------|-------------------------|------------|------------|---------------------|---------------------|--------------|---|------------|
| TO ORDER BURNDY® PRODUCTS CALL | | COLD SHRINK G SERIES OUTDOOR TERMINAL | | | | | | | | | | | | | |
| UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) | | ITEM NO: SEE TABLE | | | | | | | | | | | | | |
| CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) | | CAT. NO:SEE TABLE | | | | | | | | | | | | | |
| FOR PRODUCT INFO: http://www.burndy.com | | <table border="1"> <tr> <td>DRAWN BY: R.BABU</td> <td>12/13/2018</td> </tr> <tr> <td>CHECKER: K.JAYAVIGNESH</td> <td>9/4/2019</td> </tr> <tr> <td>DSN APRVL: K.CASTONGUAY</td> <td>10/11/2019</td> </tr> <tr> <td>MFG APRVL:</td> <td></td> </tr> <tr> <td>QA APRVL: B.ELLIOTT</td> <td>10/11/2019</td> </tr> <tr> <td>MKT APRVL: K.BOUTIN</td> <td>10/11/2019</td> </tr> </table> | | DRAWN BY: R.BABU | 12/13/2018 | CHECKER: K.JAYAVIGNESH | 9/4/2019 | DSN APRVL: K.CASTONGUAY | 10/11/2019 | MFG APRVL: | | QA APRVL: B.ELLIOTT | 10/11/2019 | MKT APRVL: K.BOUTIN | 10/11/2019 |
| DRAWN BY: R.BABU | 12/13/2018 | | | | | | | | | | | | | | |
| CHECKER: K.JAYAVIGNESH | 9/4/2019 | | | | | | | | | | | | | | |
| DSN APRVL: K.CASTONGUAY | 10/11/2019 | | | | | | | | | | | | | | |
| MFG APRVL: | | | | | | | | | | | | | | | |
| QA APRVL: B.ELLIOTT | 10/11/2019 | | | | | | | | | | | | | | |
| MKT APRVL: K.BOUTIN | 10/11/2019 | | | | | | | | | | | | | | |
| <table border="1"> <tr> <td>PROD FAM:</td> <td>DRAWING NO</td> <td>REV</td> </tr> <tr> <td>PROJECT #:</td> <td>SIZE</td> <td>50095763</td> </tr> <tr> <td>DOCUMENT TYPE: Sales</td> <td>B</td> <td>C</td> </tr> <tr> <td>REL LEVEL: Released</td> <td></td> <td>SHEET 2 OF 2</td> </tr> </table> | | PROD FAM: | DRAWING NO | REV | PROJECT #: | SIZE | 50095763 | DOCUMENT TYPE: Sales | B | C | REL LEVEL: Released | | SHEET 2 OF 2 |  | |
| PROD FAM: | DRAWING NO | REV | | | | | | | | | | | | | |
| PROJECT #: | SIZE | 50095763 | | | | | | | | | | | | | |
| DOCUMENT TYPE: Sales | B | C | | | | | | | | | | | | | |
| REL LEVEL: Released | | SHEET 2 OF 2 | | | | | | | | | | | | | |