

JACKETED CONCENTRIC NEUTRAL 15 KV						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	CONDUCTOR SIZE	PIN CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSUDI152JP1	50104212	2	YE2R25	0.57-0.90 [14.5-23]	1.1 [28]	3
CSUDI151JP1	50104859	1	YE2R25			
CSUDI1510JP1	50104214	1/0	YE25R25			
CSUDI1510JP2	50104215	1/0	YE25R25	0.71-1.26 [18-32]	1.5 [38]	3
CSUDI1520JP2	50104216	2/0	YE26R60			
CSUDI1530JP2	50104217	3/0	YE27R60			
CSUDI1540JP2	50104218	4/0	YE28R60			
CSUDI15250JP2	50104219	250	YE30R60			
CSUDI1540JP3	50104220	4/0	YE28R60	0.83-1.34 [21-34]	1.65 [42]	3
CSUDI15250JP3	50104221	250	YE30R60			
CSUDI15300JP3	50104222	300	YE30R60			
CSUDI15350JP3	50104223	350	YE32R60			
CSUDI15400JP3	50104224	400	YE32R60			
CSUDI15450JP3	50104225	450	YE361R60			
CSUDI15500JP3	50104226	500	YE361R60			
CSUDI15350JP4	50104227	350	YE32R60	1.04-1.54 [26.5-39]	1.97 [50]	3
CSUDI15400JP4	50104228	400	YE32R60			
CSUDI15450JP4	50104229	450	YE361R60			
CSUDI15500JP4	50104230	500	YE361R60			
CSUDI15550JP4	50106832	550	YE39R60			
CSUDI15600JP4	50106833	600	YE39R60			
CSUDI15650JP4	50104233	650	--			
CSUDI15700JP4	50106834	700	--			
CSUDI15750JP4	50106835	750	--			
CSUDI15750JP5	50104236	750	--	1.34-2.19 [34-55.5]	2.67 [68]	3
CSUDI15800JP5	50104237	800	--			
CSUDI15850JP5	50104238	850	--			
CSUDI151000JP5	50104239	1000	--			
CSUDI151250JP5	50104240	1250	--			
CSUDI151300JP5	50104241	1300	--			
CSUDI151500JP5	50104242	1500	--			
CSUDI151750JP5	50104243	1750	--			
CSUDI152000JP5	50104244	2000	--			

JACKETED CONCENTRIC NEUTRAL 25/28 KV						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	CONDUCTOR SIZE	PIN CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSUDI25281JP1	50104245	1	YE2R25	0.71-1.26 [18-32]	1.5 [38]	3
CSUDI252810JP1	50104246	1/0	YE25R25			
CSUDI252820JP1	50104247	2/0	YE26R60			
CSUDI252830JP1	50104248	3/0	YE27R60			
CSUDI252840JP1	50104249	4/0	YE28R60			
CSUDI252810JP2	50104250	1/0	YE25R25	0.83-1.34 [21-34]	1.65 [42]	3
CSUDI252820JP2	50104251	2/0	YE26R60			
CSUDI252830JP2	50104252	3/0	YE27R60			
CSUDI252840JP2	50104253	4/0	YE28R60			
CSUDI2528250JP2	50104254	250	YE30R60			
CSUDI2528250JP3	50104255	250	YE30R60			
CSUDI2528300JP3	50104256	300	YE30R60	1.04-1.54 [26.5-39]	1.97 [50]	3
CSUDI2528350JP3	50104271	350	YE32R60			
CSUDI2528400JP3	50104272	400	YE32R60			
CSUDI2528450JP3	50104273	450	YE361R60			
CSUDI2528500JP3	50104274	500	YE361R60			
CSUDI2528500JP4	50104275	500	YE361R60			
CSUDI2528550JP4	50104276	550	YE39R60			
CSUDI2528600JP4	50104277	600	YE39R60	1.34-2.19 [34-55.5]	2.67 [68]	3
CSUDI2528650JP4	50104278	650	--			
CSUDI2528700JP4	50104279	700	--			
CSUDI2528750JP4	50104280	750	--			
CSUDI2528800JP4	50104281	800	--			
CSUDI2528850JP4	50104282	850	--			
CSUDI25281000JP4	50104283	1000	--			
CSUDI25281250JP4	50104284	1250	--			
CSUDI25281300JP4	50104285	1300	--			
CSUDI25281500JP4	50104286	1500	--			

NOTES:

1. MATERIAL: SILICON RUBBER

2. KIT INCLUDES; (COLD SHRINK TERMINATION SUB ASSEMBLY, CTSR ENDSEAL TERMINATION, ENDSEAL TERMINATION, INSTALLATION GUIDE ,CUTBACK TEMPLATE).

3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.

4. CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.

5. CONFORMS TO ISO/IEC 17025 STANDARDS.

6. RUS APPROVED.

7. REPORT # HVS CST 181207 & # HVS CST 111209.




REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	11/07/2019	UPDATED TABLE DATA	52346	JL	KC

TO ORDER BURNDY® PRODUCTS CALL		COLD SHRINK UD SERIES INDOOR WITH PIN													
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE													
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE													
FOR PRODUCT INFO: http://www.burndy.com		<table border="1"> <tr> <td>DRAWN BY: R.BABU</td> <td>11/22/2018</td> </tr> <tr> <td>CHECKER: K.JAYAVIGNESH</td> <td>9/3/2019</td> </tr> <tr> <td>DSN APRVL: K.CASTONGUAY</td> <td>10/11/2019</td> </tr> <tr> <td>MFG APRVL:</td> <td></td> </tr> <tr> <td>QA APRVL: B.ELLIOTT</td> <td>10/11/2019</td> </tr> <tr> <td>MKT APRVL: K.BOUTIN</td> <td>10/11/2019</td> </tr> </table>		DRAWN BY: R.BABU	11/22/2018	CHECKER: K.JAYAVIGNESH	9/3/2019	DSN APRVL: K.CASTONGUAY	10/11/2019	MFG APRVL:		QA APRVL: B.ELLIOTT	10/11/2019	MKT APRVL: K.BOUTIN	10/11/2019
DRAWN BY: R.BABU	11/22/2018														
CHECKER: K.JAYAVIGNESH	9/3/2019														
DSN APRVL: K.CASTONGUAY	10/11/2019														
MFG APRVL:															
QA APRVL: B.ELLIOTT	10/11/2019														
MKT APRVL: K.BOUTIN	10/11/2019														
<table border="1"> <tr> <td>PROD FAM:</td> <td>DRAWING NO</td> <td>REV</td> </tr> <tr> <td>PROJECT #:</td> <td>SIZE</td> <td></td> </tr> <tr> <td>DOCUMENT TYPE: Sales</td> <td>50095765</td> <td>C</td> </tr> <tr> <td>REL LEVEL: Released</td> <td>B</td> <td>SHEET 1 OF 2</td> </tr> </table>		PROD FAM:	DRAWING NO	REV	PROJECT #:	SIZE		DOCUMENT TYPE: Sales	50095765	C	REL LEVEL: Released	B	SHEET 1 OF 2		
PROD FAM:	DRAWING NO	REV													
PROJECT #:	SIZE														
DOCUMENT TYPE: Sales	50095765	C													
REL LEVEL: Released	B	SHEET 1 OF 2													

BARE CONCENTRIC NEUTRAL 15 kV						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	CONDUCTOR SIZE	PIN CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSUDI152BP1	50104287	2	YE2R25	0.57-0.90 [14.5-23]	1.1 [28]	3
CSUDI151BP1	50104288	1	YE2R25			
CSUDI1510BP1	50104289	1/0	YE25R25			
CSUDI1510BP2	50104290	1/0	YE25R25	0.71-1.26 [18-32]	1.5 [38]	3
CSUDI1520BP2	50104291	2/0	YE26R60			
CSUDI1530BP2	50104292	3/0	YE27R60			
CSUDI1540BP2	50104293	4/0	YE28R60			
CSUDI15250BP2	50104294	250	YE30R60			
CSUDI1540BP3	50104295	4/0	YE28R60			
CSUDI15250BP3	50104296	250	YE30R60	0.83-1.34 [21-34]	1.65 [42]	3
CSUDI15300BP3	50104297	300	YE30R60			
CSUDI15350BP3	50104298	350	YE32R60			
CSUDI15400BP3	50104299	400	YE32R60			
CSUDI15450BP3	50104300	450	YE361R60			
CSUDI15500BP3	50104301	500	YE361R60			
CSUDI15350BP4	50104302	350	YE32R60	1.04-1.54 [26.5-39]	1.97 [50]	3
CSUDI15400BP4	50104303	400	YE32R60			
CSUDI15450BP4	50104304	450	YE361R60			
CSUDI15500BP4	50104305	500	YE361R60			
CSUDI15550BP4	50104306	550	YE39R60			
CSUDI15600BP4	50104307	600	YE39R60			
CSUDI15650BP4	50104308	650	--			
CSUDI15700BP4	50104309	700	--			
CSUDI15750BP4	50104310	750	--			
CSUDI15750BP5	50104311	750	--	1.34-2.19 [34-55.5]	2.67 [68]	3
CSUDI15800BP5	50104312	800	--			
CSUDI15850BP5	50104313	850	--			
CSUDI151000BP5	50104314	1000	--			
CSUDI151250BP5	50104315	1250	--			
CSUDI151300BP5	50104316	1300	--			
CSUDI151500BP5	50104317	1500	--			
CSUDI151750BP5	50104318	1750	--			
CSUDI152000BP5	50104319	2000	--			

NOTES:

- MATERIAL: SILICON RUBBER
-  KIT INCLUDES; (COLD SHRINK TERMINATION SUB ASSEMBLY, CTSR ENDSEAL TERMINATION, ENDSEAL TERMINATION, INSTALLATION GUIDE).
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.
- CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.
- CONFORMS TO ISO/IEC 17025 STANDARDS.
- RUS APPROVED.
- REPORT # HVS CST 181207 & # HVS CST 111209.

BARE CONCENTRIC NEUTRAL 25/28 kV						
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	CONDUCTOR SIZE	PIN CATALOG NUMBER	INSULATION DIAMETER RANGE	INSULATION DIAMETER (PRESHRINK)	STANDARD PACKAGE QUANTITY
CSUDI25281BP1	50104320	1	YE2R25	0.71-1.26 [18-32]	1.5 [38]	3
CSUDI252810BP1	50104321	1/0	YE25R25			
CSUDI252820BP1	50104322	2/0	YE26R60			
CSUDI252830BP1	50104323	3/0	YE27R60			
CSUDI252840BP1	50104324	4/0	YE28R60			
CSUDI252810BP2	50104325	1/0	YE25R25			
CSUDI252820BP2	50104326	2/0	YE26R60	0.83-1.34 [21-34]	1.65 [42]	3
CSUDI252830BP2	50104327	3/0	YE27R60			
CSUDI252840BP2	50104328	4/0	YE28R60			
CSUDI2528250BP2	50104329	250	YE30R60			
CSUDI2528250BP3	50104330	250	YE30R60			
CSUDI2528300BP3	50104331	300	YE30R60			
CSUDI2528350BP3	50104332	350	YE32R60	1.04-1.54 [26.5-39]	1.97 [50]	3
CSUDI2528400BP3	50104333	400	YE32R60			
CSUDI2528450BP3	50104334	450	YE361R60			
CSUDI2528500BP3	50104335	500	YE361R60			
CSUDI2528500BP4	50104336	500	YE361R60			
CSUDI2528550BP4	50104337	550	YE39R60			
CSUDI2528600BP4	50104338	600	YE39R60	1.34-2.19 [34-55.5]	2.67 [68]	3
CSUDI2528650BP4	50104339	650	--			
CSUDI2528700BP4	50104340	700	--			
CSUDI2528750BP4	50104341	750	--			
CSUDI2528800BP4	50104342	800	--			
CSUDI2528850BP4	50104343	850	--			
CSUDI25281000BP4	50104344	1000	--			
CSUDI25281250BP4	50104345	1250	--			
CSUDI25281300BP4	50104346	1300	--			
CSUDI25281500BP4	50104347	1500	--			



TO ORDER BURNDY® PRODUCTS CALL		COLD SHRINK UD SERIES INDOOR WITH PIN	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: R.BABU 11/22/2018	
		CHECKER: K.JAYAVIGNESH 9/3/2019	
		DSN APRVL: K.CASTONGUAY 10/11/2019	
		MFG APRVL: [blank]	
		QA APRVL: B.ELLIOTT 10/11/2019	
		MKT APRVL: K.BOUTIN 10/11/2019	
		PROD FAM: [blank]	
		DRAWING NO	
		50095765	
		REV	
		C	

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	11/07/2019	UPDATED TABLE DATA	52346	JL	KC