

MEDIUM VOLTAGE SLEEVES OUTDOOR WITH BOOT BARE CONCENTRIC 5kV/8kV				
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	STANDARD PACKAGE QUANTITY
CS3CO58220B	50104768	#2	0.61-0.82 [15.5 - 20.8]	1
		1		
		1/0		
		2/0		
CS3CO5820350B	50104769	2/0	0.72 - 1.10 [18.3 - 27.9]	1
		3/0		
		4/0		
		250		
		350		

MEDIUM VOLTAGE SLEEVES OUTDOOR WITH BOOT BARE CONCENTRIC 25kV / 28kV				
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	STANDARD PACKAGE QUANTITY
CS3CO2528140B	50104774	#1	0.80-1.27 [20.3 - 32.3]	1
		1/0		
		2/0		
		3/0		
		4/0		
CS3CO2528250500B	50104775	250	1.10 - 1.52 [27.9 - 38.6]	1
		300		
		350		
		400		
		450		
		500		

MEDIUM VOLTAGE SLEEVES OUTDOOR WITH BOOT BARE CONCENTRIC 28kV / 35kV				
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	STANDARD PACKAGE QUANTITY
CS3CO2835250500B	50104777	250	1.10 - 1.52 [27.9 - 38.6]	1
		300		
		350		
		400		
		450		
		500		



**WITH BOOT**

- NOTES:
- MATERIAL: SILICONE RUBBER
  - KIT INCLUDES; (COLD SHRINKABLE TUBE, UNPRINTED, 3-LEG BOOT, SEAL-ANTI TRACK , CABLE TIE, CST INSTALLATION GUIDE, POLY BAG)
  - DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.
  - CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.
  - CONFORMS TO ISO/IEC 17025 STANDARDS.
  - RUS APPROVED.
  - THE TITAN 3MOD KITS ARE DESIGNED TO BE USED WITH TITAN TERMINATORS TO CONVERT 3/C SHIELDING POWER CABLES TO 3-1/C CABLE TERMINATORS.

REV	DATE	DESCRIPTION	EC	BY	C'H'K.
D	03/09/2021	NOTES UPDATION	210308005677	WP	RRA


TO ORDER BURNDY® PRODUCTS CALL  UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)  CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)  FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>	COLD SHRINK 3C CONVERSION SERIES		
	ITEM NO: SEE TABLE		
	CAT. NO: SEE TABLE		
	DRAWN BY: R. BABU	12/13/2018	
	CHECKER: K. JAYAVIGNESH	9/4/2019	
DSN APRVL: K. CASTONGUAY	10/11/2019		
MFG APRVL: B. ELLIOTT	12/30/1899		
QA APRVL: B. ELLIOTT	10/11/2019		
MKT APRVL: K. BOUTIN	10/11/2019		
PROD FAM:	DRAWING NO	REV	
PROJECT #:	SIZE	50095782	
DOCUMENT TYPE: Sales	B	D	
REL LEVEL: Released		SHEET 1 OF 2	

MEDIUM VOLTAGE SLEEVES INDOOR WITHOUT BOOT JACKETED CONCENTRIC 5kV/8kV				
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	STANDARD PACKAGE QUANTITY
CS3CI58220J	50104778	#2	0.61-0.82 [15.5 - 20.8]	1
		1		
		1/0		
		2/0		
CS3CI5820350J	50104779	2/0	0.72 - 1.10 [18.3 - 27.9]	1
		3/0		
		4/0		
		250		
		350		

MEDIUM VOLTAGE SLEEVES INDOOR WITHOUT BOOT JACKETED CONCENTRIC 25kV / 28kV				
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	STANDARD PACKAGE QUANTITY
CS3CI2528140J	50104784	#1	0.80-1.27 [20.3 - 32.3]	1
		1/0		
		2/0		
		3/0		
		4/0		
CS3CI2528250500J	50104785	250	1.10 - 1.52 [27.9 - 38.6]	1
		300		
		350		
		400		
		450		

MEDIUM VOLTAGE SLEEVES INDOOR WITHOUT BOOT JACKETED CONCENTRIC 28kV/35kV				
BURNDY KIT CATALOG NUMBER	BURNDY KIT ITEM NUMBER	SLEEVE RANGE	INSULATION DIAMETER RANGE	STANDARD PACKAGE QUANTITY
CS3CI2835250500J	50104787	250	1.33 - 1.75 [33.8 - 44.5]	1
		300		
		350		
		400		
		450		




NOTES:

- MATERIAL: SILICONE RUBBER
-  KIT INCLUDES; (COLD SHRINKABLE TUBE, SEAL-ANTI TRACK, CABLE TIE, CST INSTALLATION GUIDE, POLY BAG)
- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.
- CONFORMS TO IEEE-48-2009, CLASS 1 STANDARDS.
- CONFORMS TO ISO/IEC 17025 STANDARDS.
- RUS APPROVED.
- THE TITAN 3MOD KITS ARE DESIGNED TO BE USED WITH TITAN TERMINATORS TO CONVERT 3/C SHIELDING POWER CABLES TO 3-1/C CABLE TERMINATORS.



**WITHOUT BOOT**

REV	DATE	DESCRIPTION	EC	BY	C'H'K.
D	03/09/2021	NOTES UPDATION	210308005677	WP	RRA

TO ORDER BURNDY® PRODUCTS CALL		COLD SHRINK 3C CONVERSION SERIES															
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE															
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE															
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		<table border="1"> <tr> <td>DRAWN BY: R.BABU</td> <td>12/13/2018</td> <td rowspan="5"></td> </tr> <tr> <td>CHECKER: K.JAYAVIGNESH</td> <td>9/4/2019</td> </tr> <tr> <td>DSN APRVL: K.CASTONGUAY</td> <td>10/11/2019</td> </tr> <tr> <td>MFG APRVL: B.ELLIOTT</td> <td>12/30/1899</td> </tr> <tr> <td>QA APRVL: B.ELLIOTT</td> <td>10/11/2019</td> </tr> <tr> <td>MKT APRVL: K.BOUTIN</td> <td>10/11/2019</td> <td></td> </tr> </table>		DRAWN BY: R.BABU	12/13/2018		CHECKER: K.JAYAVIGNESH	9/4/2019	DSN APRVL: K.CASTONGUAY	10/11/2019	MFG APRVL: B.ELLIOTT	12/30/1899	QA APRVL: B.ELLIOTT	10/11/2019	MKT APRVL: K.BOUTIN	10/11/2019	
DRAWN BY: R.BABU	12/13/2018																
CHECKER: K.JAYAVIGNESH	9/4/2019																
DSN APRVL: K.CASTONGUAY	10/11/2019																
MFG APRVL: B.ELLIOTT	12/30/1899																
QA APRVL: B.ELLIOTT	10/11/2019																
MKT APRVL: K.BOUTIN	10/11/2019																
PROJ FAMIL: SALES		DRAWING NO: 50095782															
REL LEVEL: Released		REV: D															