




REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	03/28/2019	NEW DRAWING CREATION	51162	RB	VS



NOTES:

1. MATERIAL: COPPER
2. ACCOMODATES: 4/0 (Ø.552) 7, 9, 12 STR. COPPER CABLE.
3. LETTERING ON CONNECTOR:
 BURNDY YCA282N90
 USE DIE 168 K840
 4/0 7 12 19
4. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED.

TO ORDER BURNDY® PRODUCTS CALL		HYLUG™	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 10002092	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: YCA282N90	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: R.BABU 03/28/2019	
		CHECKER: V.SAKTHIVEL 03/28/2019	
		DSN APRVL: G.SCHRADER 12/04/2019	
		MFG APRVL: --	
		QA APRVL: B.ELLIOTT 04/05/2019	
		MKT APRVL: J.HALL 05/06/2019	
		PROD FAM: CM&R COMPRESSION	
PROJECT #:	--	SIZE	D
DOCUMENT TYPE:	SALES		
REL LEVEL:	Released		
		DRAWING NO	50100070
		REV	A
		SHEET 1 OF 1	