

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	10/22/2019	UPDATED DRAWING	52366	JL	TR

**FEATURES:**

ACCOMMODATES BOTH FLEX AND CODE CONDUCTORS




cULus LISTED TO UL1953 (FILE# E74460)

AL9CU RATED


100ka SCCR RATING WITH CORRECT FUSING

600V VOLTAGE RATING


CONTACT CUSTOMER SERVICE FOR ALTERNATE CONFIGURATIONS AT TELEPHONE NUMBER 1 800 346-4175



RUN SIDE



DOUBLE WIDE STYLE



TAP SIDE

BDB L CS 10 L V 1 DW

- DOUBLE WIDE
- NUMBER OF POLES (1,2 OR 3)
- TAP CONFIGURATION IDENTIFIER (SEE TABLE)
- L FOLLOWING DIGIT FOR LAY-IN
- RUN CONFIGURATION IDENTIFIER (SEE TABLE)
- CONFIGURABLE SERIES
- LARGE SIZE
- BURNDY DISTRIBUTION BLOCK

**NOTES:**

- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- MATERIALS: BASE AND POLE SEPERATING SIDES - NYLON 6/6  
BLOCK AND RETENTION SCREWS - TIN PLATED ALUMINUM  
BLOCK MOUNTING HARDWARE - STAINLESS STEEL

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES  
1-800-346-4175 (LONDONDERRY, NH)

CANADA:  
1-800-361-6975 (QUEBEC)  
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

LAY-IN DISTRIBUTION BLOCKS

ITEM NO: SEE TABLE		DRAWING NO	
CAT. NO: SEE TABLE		REV	
DRAWN BY: T. REYNOLDS	6/21/2019		B
CHECKER:			
DSN APRVL: T. REYNOLDS	10/16/2019		
MFG APRVL: P. MARTEL	10/17/2019		
QA APRVL: C. LINDQUIST	10/16/2019		
MKT APRVL: R. ROBICHEAU	10/16/2019	PROJECT #: NPD-02495	SIZE
PROD FAM: --		50101541	
DOCUMENT TYPE: SALES		B	
REL LEVEL: Released			SHEET 1 OF 3


**BURNDY LARGE DISTRIBUTION BLOCKS**

OPEN STYLE BLOCKS	BLOCK						AMPACITY		
	RUN			TAP					
	HOLE LAYOUT	RANGE	TORQUE in-lbs	HOLE LAYOUT	RANGE	TORQUE in-lbs			
BDBLCS10LV1DW	O (1)	500 - 750 B, C, H, I, K, 777 DLO	500-750	700	OO (2)	#4 awg - 500	#4-4/0	400	475
BDBLCS10LV2DW						B, C, H, I, K, 535 DLO	250-535	600	
BDBLCS10LV3DW									
BDBLCS10LR1DW	O (1)	500 - 750 B, C, H, I, K, 777 DLO	500-750	700	OOOO (4)	#6 awg - 4/0 B, C, H, I, K, DLO	#6-2/0	180	475
BDBLCS10LR2DW						3/0-4/0	300		
BDBLCS10LR3DW									
BDBLCS10LK1DW	O (1)	500 - 750 B, C, H, I, K, 777 DLO	500-750	700	OOO (6)	#14 awg - 2/0	#14-#4	80	475
BDBLCS10LK2DW						B, C, H, I, K, DLO	#2-2/0	120	
BDBLCS10LK3DW									
BDBLCS10LA1DW	O (1)	500 - 750 B, C, H, I, K, 777 DLO	500-750	700	OOOOOO (12)	#14 awg - #4	#12-#8 AL	10	475
BDBLCS10LA2DW						awg B, C, H, I, K, DLO	#14-#8 CU	15	
BDBLCS10LA3DW							#6-#4	30	
BDBLCS13LV1DW	O (1)	750 - 1000 B, C, H, I, K, 1111 DLO	750-1000	700	OO (2)	#4 awg - 500	#4-4/0	400	545
BDBLCS13LV2DW						B, C, H, I, K, 535 DLO	250-535	600	
BDBLCS13LV3DW									
BDBLCS13LR1DW	O (1)	750 - 1000 B, C, H, I, K, 1111 DLO	750-1000	700	OOOO (4)	#6 awg - 4/0 B, C, H, I, K, DLO	#6-2/0	180	545
BDBLCS13LR2DW						3/0-4/0	300		
BDBLCS13LR3DW									
BDBLCS13LK1DW	O (1)	750 - 1000 B, C, H, I, K, 1111 DLO	750-1000	700	OOO (6)	#14 awg - 2/0	#14-#4	80	545
BDBLCS13LK2DW						B, C, H, I, K, DLO	#2-2/0	120	
BDBLCS13LK3DW									
BDBLCS13LA1DW	O (1)	750 - 1000 B, C, H, I, K, 1111 DLO	750-1000	700	OOOOOO (12)	#14 awg - #4	#12-#8 AL	10	545
BDBLCS13LA2DW						awg B, C, H, I, K, DLO	#14-#8 CU	15	
BDBLCS13LA3DW							#6-#4	30	

RUN SIDE		
DIGIT	HOLE LAYOUT	RANGE
10	O	500 kcmil - 750 kcmil
13	O	750 kcmil - 1000 kcmil

TAP SIDE		
LETTER	HOLE LAYOUT	RANGE
A	OOOOOO OOOOOO	#14 awg - #4 awg
B	OOO OOO	
C	OO OO	
D	OO	
E	O	
F	OOO OOO	#14 awg - #2 awg
G	OO OO	
H	OO	
J	O	
K	OOO OOO	#14 awg - 2/0
M	OO OO	
N	OO	
P	O	
R	OO OO	#6 awg - 4/0
T	OO	#6 awg - 350 kcmil
U	O	
V	OO	#4 awg - 500 kcmil
W	O	
X	OOOOO	
Y	OO	#4 awg - 600 kcmil
Z	OOOOO	#4 awg - 600 kcmil


TO ORDER BURNDY® PRODUCTS CALL  
 UNITED STATES  
 1-800-346-4175 (LONDONDERRY, NH)  
 CANADA:  
 1-800-361-6975 (QUEBEC)  
 1-800-387-6487 (ALL OTHER PROVINCES)  
 FOR PRODUCT INFO: <http://www.burndy.com>

LAY-IN DISTRIBUTION BLOCKS			
ITEM NO: SEE TABLE			
CAT. NO: SEE TABLE			
DRAWN BY: T. REYNOLDS	6/21/2019		
CHECKER:			
DSN APRVL: T. REYNOLDS	10/16/2019		
MFG APRVL: P. MARTEL	10/17/2019		
QA APRVL: C. LINDQUIST	10/16/2019		
MKT APRVL: R. ROBICHEAU	10/16/2019	PROJ. NO: NPD-02495	
PROD FAM: --		SIZE	DRAWING NO
DOCUMENT TYPE: SALES		B	50101541
REL LEVEL: Released			SHEET 2 OF 3

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	10/22/2019	UPDATED DRAWING	52366	JL	TR

SCCR FUSE VALUES							
OPEN STYLE	J	T	RK1	RK5	G	CC	L
BDBLCS10LV1DW	200	200	100	30	60	30	200
BDBLCS10LV2DW	200	200	100	30	60	30	200
BDBLCS10LV3DW	200	200	100	30	60	30	200
BDBLCS10LR1DW	200	200	100	30	60	30	200
BDBLCS10LR2DW	200	200	100	30	60	30	200
BDBLCS10LR3DW	200	200	100	30	60	30	200
BDBLCS10LK1DW	200	200	100	30	60	30	200
BDBLCS10LK2DW	200	200	100	30	60	30	200
BDBLCS10LK3DW	200	200	100	30	60	30	200
BDBLCS10LA1DW	200	200	100	30	60	30	200
BDBLCS10LA2DW	200	200	100	30	60	30	200
BDBLCS10LA3DW	200	200	100	30	60	30	200
BDBLCS13LV1DW	200	200	100	30	60	30	200
BDBLCS13LV2DW	200	200	100	30	60	30	200
BDBLCS13LV3DW	200	200	100	30	60	30	200
BDBLCS13LR1DW	200	200	100	30	60	30	200
BDBLCS13LR2DW	200	200	100	30	60	30	200
BDBLCS13LR3DW	200	200	100	30	60	30	200
BDBLCS13LK1DW	200	200	100	30	60	30	200
BDBLCS13LK2DW	200	200	100	30	60	30	200
BDBLCS13LK3DW	200	200	100	30	60	30	200
BDBLCS13LA1DW	200	200	100	30	60	30	200
BDBLCS13LA2DW	200	200	100	30	60	30	200
BDBLCS13LA3DW	200	200	100	30	60	30	200

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	10/22/2019	UPDATED DRAWING	52366	JL	TR

<p>TO ORDER BURNDY® PRODUCTS CALL</p> <p>UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)</p> <p>CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)</p> <p>FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a></p>	LAY-IN DISTRIBUTION BLOCKS		
	ITEM NO: SEE TABLE		
	CAT. NO: SEE TABLE		
	DRAWN BY: T. REYNOLDS	6/21/2019	
	CHECKER:		
	DSN APRVL: T. REYNOLDS	10/16/2019	
	MFG APRVL: P. MARTEL	10/17/2019	
	QA APRVL: C. LINDQUIST	10/16/2019	
	MKT APRVL: R. ROBICHEAU	10/16/2019	
	PROD FAM: --	DRAWING NO	REV
PROJECT #: NPD-02495	SIZE	50101541	
DOCUMENT TYPE: SALES	B	B	
REL LEVEL: Released		SHEET 3 OF 3	