



NOTES:

1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
2. BOX VOLUME: 45.0 IN³ [737.4 CM³]
3. ACCEPTS # 971 PARTITION , SOLD SEPARATELY
4. ACCEPTS # 701FG GANGABLE PROTECTOR PLATE , SOLD SEPARATELY
5. UL LISTED

KNOCKOUTS -SINGLE GANG BOX	
TRADE SIZE	LOCATION
1/2", 3/4" CONC. KO'S	4- TOP
	4- BOTTOM
	4- BACK
	2- EACH SIDE

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDES	STEEL	GALVANIZED

SYMBOL	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	K.K.	

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE: **TWO GANG 3-1/2" DEEP WELDED MASONRY BOX**

<small>TOLERANCE UNLESS OTHERWISE SPECIFIED</small> .XX DECIMAL ±.015 .XXX DECIMAL ±.005 ANGLE ±2°	RACO South Bend, Indiana		SCALE: 1:2
	DRAWN BY:	K.K.	
	APP. BY:	N.S.	
	DATE:	1/26/2015	