


2X #8-32 UNC
THRU ALL



- NOTES:
 1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. VOLUME: 4.0 IN³ [66.0 CM³]
 3. UL LISTED

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COVER	STEEL	GALVANIZED

756 CUS

SYMBOL	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	RMV	03/02/18

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
**4"SQ. OPEN FIXTURE COVER
 RAISED 5/8"**

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL ±.015
 .XXX DECIMAL ±.005
 ANGLE ±2°

RACO
 South Bend, Indiana

DRAWN BY:	RMV
APP. BY:	N.S.
DATE:	03/02/18

SCALE:
 1:2

756

DIMENSION SHEET FOR CAT. NO.

SIZE:
A

8.5in*11in