



- NOTES:  
 1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]  
 2. VOLUME: 8.5 IN<sup>3</sup> [139.3 CM<sup>3</sup>]  
 3. UL LISTED

**LIST OF PARTS**

DESCRIPTION	MATERIAL	FINISH
COVER	STEEL	GALVANIZED

758 CUS

	INITIAL RELEASE	RMV	03/02/18
SYM.	REVISION DESCRIPTION	APP	DATE

758

DIMENSION SHEET FOR CAT. NO.

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:  
**4" SQ OPEN FIXTURE COVER  
 RAISED 1.25" W/ EARS**

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL ±.015  
 .XXX DECIMAL ±.005  
 ANGLE ±2°

**RACO**  
 South Bend, Indiana

DRAWN BY:	RMV
APP. BY:	N.S.
DATE:	03/02/18

SCALE:  
 1:2

SIZE:

**A**

8.5in\*11in