


NOTES:

1. ALL GUY WIRE DEAD-ENDS MEET 100% OF THE WIRE RATED BREAKING STRENGTH (RBS) AS SHOWN IN TABLE 1.
2. B-COAT BEZINAL PER ASTM A855. B-COAT IS STANDARD.
3. HAND LAY STANDARD DIRECTION: LEFT
4. ALL DIMENSIONS ARE FOR REFERENCE ONLY



IDENTIFICATION TAGS

CATALOG NO.	TABLE 1			COLOR	STRAND		APPLICATION RANGE	RBS (POUNDS)	STANDARD PACK QUANTITY
	1	2	3		SIZE	CONSTRUCTION			
BDE9102	20	0.75	0.9375	RED	3/16	7W 7W	0.174 TO 0.203 in (4.420 TO 5.156 mm)	3900	100
BDE9104	25	0.75	1.0000	YELLOW	1/4	3W 7W	0.231 TO 0.259 in (5.867 TO 6.579 mm)	6650	50
BDE9106	31	0.75	1.0625	BLACK	5/16	3W 7W 7W	0.292 TO 0.336 in (7.417 TO 8.534 mm)	11200	50
BDE9107	35	0.75	1.0625	ORANGE	3/8	3W 7W	0.337 TO 0.394 in (8.560 TO 10.008 mm)	15400	50
BDE9108	38	1.00	1.1250	GREEN	7/16	7W	0.395 TO 0.474 in (10.033 TO 12.040 mm)	20800	25
BDE9115	49	1.00	1.875	BLUE	1/2	7W 19W	0.475 TO 0.515 in (12.065 TO 13.081 mm)	26900	20
BDE9116	55	1.00	1.875	YELLOW	9/16	7W 19W	0.516 TO 0.570 in (13.106 TO 14.478 mm)	35000	10

64848	4/21/16	JES	JES	FARGO®	HUBBELL® POWER SYSTEMS
EC #	DATE	CHG BY	RESP ENG		
DESC OF DWG: ADDED BDE2115 AND BDE2116 -- -- REASON (S) FOR CHANGE: -- DISPOSITION OF MAT'L: --				TITLE CUSTOMER DWG BDE FORMED WIRE	
SIZE B		DWG NO. CC-21376		CAT / PART / ASSY NO. SEE CHART	
DO NOT SCALE THIS DRAWING		DRN BY LEB		DATE 08/16/13	
				REV 03	
				SHEET 1 OF 1	