



Log in | Register

search



Switch to

Products ▼ Market ▼ Solutions ▼ Resources ▼ About Us ▼

Start --> Search=C11DRK* --> C11DRK



C11DRK

Cast Bronze Body Ground Clamp, Conductor Range (Main/Primary):10 - 2 AWG Stranded

[Image](#) | [Line Art](#) | [3D Model](#) | [Video](#) | [Customer Drawing](#)

- [Email Datasheet](#)
- [Print Datasheet](#)
- [Add to Favorites](#)

[Specifications](#) | [Documents](#)

Dimensional **General** **Conductor(s)** **Approvals / Certifications** **Other Features**

Dimensional	
Pipe Size (Range)	N/A
General	
Product Description	Cast Bronze Body Ground Clamp, Conductor Range (Main/Primary):10 - 2 AWG Stranded
Conductor(s)	
Rebar Size (Range)	N/A
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	N/A
Approvals / Certifications	
UL Listed	Y
ROHS Compatible	Compliant
Other Features	

UPC	7818103596799
-----	---------------

© BURNDY® LLC 2011-2013 | [Distributors](#) | [Sales](#) | [Terms of Use](#) | [Site Map](#)

