



Log in | Register

search



Switch to

Products ▼ Market ▼ Solutions ▼ Resources ▼ About Us ▼

Start --> Search=C22DRK\* --> C22DRK



Active

## C22DRK

Cast Bronze Body Ground Clamp, Conductor  
 Range (Main/Primary): 10 - 2 AWG  
 Stranded, Length: 3.63 IN, Installation Torque: 50  
 IN-LB For Pipe

[Image](#) | [Line Art](#) | [3D Model](#) | [Video](#) |  
[Customer Drawing](#)

- [Email Datasheet](#)
- [Print Datasheet](#)
- [Add to Favorites](#)

[Specifications](#) | [Documents](#) |

### Dimensional    General    Conductor(s)    Approvals / Certifications    Other Features

Dimensional	
Pipe Size (Range)	N/A
General	
Product Description	Cast Bronze Body Ground Clamp, Conductor Range (Main/Primary): 10 - 2 AWG Stranded, Length: 3.63 IN, Installation Torque: 50 IN-LB For Pipe
Conductor(s)	
Rebar Size (Range)	N/A
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	N/A
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y

ROHS Compatible	Compliant
<b>Other Features</b>	
UPC	7818103597300

© BURNDY® LLC 2011-2013 | [Distributors](#) | [Sales](#) | [Terms of Use](#) | [Site Map](#)

