



VIEW A-A



INSULATION:
1 1/2 [38] THICK

LIFTING HANDLE
4 PLACES

NOTES:

- HEAT IS PROVIDED BY (1) 1500 & (1) 1900 WATT, 120V SINGLE PHASE HEATERS. FOR UNHEATED VERSION REPLACE THE PREFIX "H" WITH AN "L".
- INTERNAL DIMENSIONS: 54 [1372]W X 112 [2845]L X 75 [1905]H
- FOR RECOMMENDED SLAB SIZE ADD 9" [229] TO THE ENCLOSURE EXTERIOR.


76 1/2 [1943]

SEE NOTE 1

10W [254] X 6 1/2L [165]
DRAINPORT (4 PLACES)

LOCKABLE HANDLE

44W [1118] X 72 1/2 [1842]
REMOVABLE ACCESS PANEL
(4 PLACES)

HOTBOX ENCLOSURES ARE NON-RETURNABLE. A SIGNED DRAWING MUST BE RETURNED AT THE TIME OF ORDER. DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.					
DRN	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.hot-box.com	LOC
CHK	KPE	10/5/09	389#		LC
ENG			176kg		S
APR			SCALE		REV
APR			NTS		A
PROJECT NUMBER			SIZE	DRAWING DESCRIPTION	10/09
091102			B		
SHEET 1 OF 1			HOT BOX® (2 SECTION) ALUMINUM ENCLOSURE HB10FN-DT		DRAWING NUMBER
					HA054112075