


ITEM	DESCRIPTION	QTY
1	15 PIN MALE HD-SUB CONNECTOR	1
2	8 PIN FEMALE MINI DIN CONNECTOR	1
3	MINI COAXIAL CABLE BLACK	8"
4	1" OD SHRINK TUBE 4" LONG BLACK	1
5	CABLE TIE	1

CATALOG NUMBER	DESCRIPTION
15M6P1	6" PIGTAIL HIGH DENSITY D-SUB 15 MALE TO MINI DIN 8 FEMALE, 1 PACK
15M6P10	6" PIGTAIL HIGH DENSITY D-SUB 15 MALE TO MINI DIN 8 FEMALE, 10 PACK
15MP6P1	6" PIGTAIL HIGH DENSITY D-SUB 15 MALE TO MINI DIN 8 FEMALE, 1 PACK, PLENUM RATED
15MP6P10	6" PIGTAIL HIGH DENSITY D-SUB 15 MALE TO MINI DIN 8 FEMALE, 10 PACK, PLENUM RATED



NOTES:

1. CONTACTS: GOLD PLATED 2u".
2. 15-PIN CONNECTOR SIDE MOUNTS TO AN INFINeSTATION MODULE PLATE LOADED WITH A FEMALE Plug-n-Play VGA HORIZONTAL CABLE OR AN AV CONNECTOR USING TWO THUMB SCREWS.
3. 8-PIN CONNECTOR SIDE CONNECTS TO Plug-n-Play VGA HORIZONTAL CABLE. MOLDED IN EARS ON 8-PIN SIDE TO ACCOMMODATE A WIRE-TIE FOR ADDED STRAIN RELIEF.
4. CABLE IS MINI COAXIAL CABLE, 75 Ohm.
5. FOR USE WITH VIDEO DISTRIBUTION DEVICES SUCH AS PROJECTORS, CAMERAS, AND COMPUTERS.
6. PIGTAIL, CABLE TIE, AND SHRINK TUBING SOLD IN SINGLE PACKS OR IN PACKAGES OF 10.
7. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTIFICATION.

A	6538	05/02/08	INITIAL RELEASE	BTM	
REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY

Created on UNIGRAPHICS

DIMENSIONING AND TOLERANCING PER
ANSI Y14.5M-1982.
UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [MM].
TOLERANCES
.XX = ±.01 [.25]
.XXX = ±.005 [.13]
.XXXX = ±.0025 [.06]
ANGLE TOL ±1°

IN ACCEPTING OUR DRAWINGS,
BLUEPRINTS, OR SUPPORTING
DOCUMENTATION FOR QUOTATION
OR OTHER PURPOSES, YOU AGREE
NOT TO DISCLOSE TO OTHERS
THE IDEAS, INFORMATION, OR
DESIGNS SHOWN HEREIN, AND
THAT YOU WILL MAKE NO USE
OF SAME WITHOUT PERMISSION.

COMPONENTS CONTAINED IN THIS DOCUMENT MUST ADHERE TO ENVIRONMENTAL SPEC. HWS12367

PROJECT REFERENCE:
015-08



Hubbell Premise Wiring
HUBBELL INCORPORATED (Delaware)

14 Lord's Hill Road, Stonington, Connecticut 06378

MATERIAL:
SEE BOM

DRAWN BY:
B MARTINO 05/02/08

CHECKED BY:

APPROVED BY:

SIZE DRAWING NO.
B HWS12678C

SCALE: NONE SHEET 1 OF 1

REV. A