



CATALOG NUMBER	COLOR	DESCRIPTION
NS730I	IVORY	1 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS730W	WHITE	1 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS730AL	ALMOND	1 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS730	BROWN	1 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS732I	IVORY	1 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 6 CONDUCTOR
NS732W	WHITE	1 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 6 CONDUCTOR
NS732AL	ALMOND	1 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 6 CONDUCTOR
NS732	BROWN	1 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 6 CONDUCTOR
NS742I	IVORY	2 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS742W	WHITE	2 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS742AL	ALMOND	2 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS744I	IVORY	2 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 6 CONDUCTOR
NS744W	WHITE	2 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 6 CONDUCTOR
NS744AL	ALMOND	2 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 6 CONDUCTOR
NS744	BROWN	2 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 6 CONDUCTOR
NS735I	IVORY	1 JACK, MIDSIZE, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS735W	WHITE	1 JACK, MIDSIZE, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS735AL	ALMOND	1 JACK, MIDSIZE, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS735	BROWN	1 JACK, MIDSIZE, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS745I	IVORY	2 JACK, MIDSIZE, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS745W	WHITE	2 JACK, MIDSIZE, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS730LA	LIGHT ALMOND	1 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS732LA	LIGHT ALMOND	1 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 6 CONDUCTOR
NS735LA	LIGHT ALMOND	1 JACK, MIDSIZE, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS742LA	LIGHT ALMOND	2 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 4 CONDUCTOR
NS744LA	LIGHT ALMOND	2 JACK, STANDARD, 1 GANG PLATE, 6-POSITION, 6 CONDUCTOR


ITEM NO.	DESCRIPTION	QTY.
1	PLATE, X PORT (SEE TABULATION)	1
2	SCREW, 6-32 X 1" LG OVAL HEAD MACHINE SCREW	4

NOTES
UNLESS OTHERWISE SPECIFIED:

- UL LISTED: E129878
- CSA CERTIFIED: LR 80837
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE



STANDARD-SIZE PLATE
6 POSITION, 4 OR 6 CONDUCTOR
SEE TABULATION



REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
B	6116	06/05/07	ADDED NS742LA AND NS744LA	BTM	
A	5813	03/10/06	INITIAL RELEASE	NJR	MMA

Created on AUTOCAD

DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM).
TOLERANCES
.XX = ±.01 (.25)
.XXX = ±.005 (.127)
.XXXX = ±.0025 (.0635)
ANGLE TOL ±1°

IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION

PROJECT REFERENCE:

MATERIAL:

DRAWN BY:
NANCY RICHARDS 03/10/06

CHECKED BY:
N. HERRING 03/10/06

APPROVED BY:
M.M. ABBY 03/10/06

HUBBELL Hubbell Premise Wiring
HUBBELL INCORPORATED (Delaware)
14 Lord's Hill Road, Stonington, Connecticut 06378

TITLE:
NET SELECT WALL PLATE 1 GANG
6 POSITION, 4 OR 6 CONDUCTOR - PHONE JACK

SIZE: D DRAWING NO. CHWS12361

SCALE: 1/1 SHEET 1 OF 1