



Log in | Register

search



Switch to

- Products ▼
- Market ▼
- Solutions ▼
- Resources ▼
- About Us ▼

Start --> Search=HSB12FR250FT* --> HSB12FR250FT



HSB12FR250FT

Polyvinyl Chloride, Thin-Wall, Flexible Heat Shrinkable Tube, 600 V, Black, Standard reel size:250 ft

[Image](#) | [Line Art](#) | [3D Model](#) | [Video](#) | [Customer Drawing](#)

- [Email Datasheet](#)
- [Print Datasheet](#)
- [Add to Favorites](#)

- Specifications
- Accessories

- General**
- Approvals / Certifications**
- Physical**
- Other Features**

General	
Product Description	Polyvinyl Chloride, Thin-Wall, Flexible Heat Shrinkable Tube, 600 V, Black, Standard reel size:250 ft
Approvals / Certifications	
UL Listed	N
CULUS	N
ROHS Compatible	Compliant
UL Recognized	Y
Physical	
Color	Black
Other Features	
UPC	7818100385366

