





CATALOG	DESCRIPTION	"A"	"B"	"C"	"D"
HHR45U10	RELAY RACK,45RU,86"H,19"W,10"D, BLACK	10.00"	22.00"	9.00"	6.00"
HHR45U16	RELAY RACK,45RU,86"H,19"W,16"D, BLACK	16.00"	28.00"	15.00"	12.00"
HHR45U16W	RELAY RACK,45RU,86"H,19"W,16"D, WHITE	16.00"	28.00"	15.00"	12.00"



GROUNDING/BONDING PROVISION, REMOVE MASKING TO EXPOSE BARE METAL AREA 4 PLACES



DETAIL A  
SCALE .75



HHR45U10 SHOWN

- NOTES:
1. MATERIAL: UPRIGHTS: ALUMINUM  
BASE PLATES: ALUMINUM  
TOP PLATE: COLD ROLLED STEEL
  2. SURFACE FINISH: POWDER PAINT, SEE TABLE FOR COLOR
  3. U/L LISTED: E129878
  4. RACK IS DELIVERED UNASSEMBLED
  5. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
3	23774	2/21/19	ADDED WHITE CATALOG TO TABLE	DPO	MMA

Created on INVENTOR

DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM).  
TOLERANCES: XX = ±.01 (.25)  
.XXX = ±.005 (.127)  
.XXXX = ±.0025 (.0635)  
ANGLE TOL ±1°

IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION

PROJECT REFERENCE:  
NPD 00048

MATERIAL:

DRAWN BY:  
D.O'CONNOR 8/27/15

CHECKED BY:

APPROVED BY:

**HUBBELL** Hubbell Premise Wiring  
HUBBELL INCORPORATED (Delaware)  
23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355

TITLE: CABLE MANAGEMENT RELAY RACK		REV. <b>3</b>
SIZE <b>D</b>	DRAWING NO. <b>HWS14487C</b>	
SCALE:	SHEET <b>1</b> OF <b>1</b>	