






CATALOG	DESCRIPTION		
HJS6	JACK, CAT6, UNI, SHIELDED, NO COLORED FACE	HJS6BN	JACK,CAT6,UNI,SHIELDED,BROWN FACE
HJS6A	JACK, CAT6A, UNI, SHIELDED, NO COLORED FACE	HJS6EI	JACK,CAT6,UNI,SHIELDED,IVORY FACE
HJS624	JACK, CAT6, UNI, SHIELDED, 24PK, NO COLORED FACE	HJS6GL	JACK,CAT6,UNI,SHIELDED,GOLD FACE
HJS6A24	JACK, CAT6A, UNI, SHIELDED, 24PK, NO COLORED FACE	HJS6OW	JACK,CAT6,UNI,SHIELDED,OFF.WHITE FACE
HJS6B	JACK,CAT6,UNI,SHIELDED,BLUE FACE	HJS6P	JACK,CAT6,UNI,SHIELDED,PURPLE FACE
HJS6BK	JACK,CAT6,UNI,SHIELDED,BLACK FACE	HJS6PK	JACK,CAT6,UNI,SHIELDED,PINK FACE
HJS6GN	JACK,CAT6,UNI,SHIELDED,GREEN FACE	HJS6ABN	JACK,CAT6A,UNI,SHIELDED,BROWN FACE
HJS6GY	JACK,CAT6,UNI,SHIELDED,GRAY FACE	HJS6AEI	JACK,CAT6A,UNI,SHIELDED,IVORY FACE
HJS6OR	JACK,CAT6,UNI,SHIELDED,ORANGE FACE	HJS6AGL	JACK,CAT6A,UNI,SHIELDED,GOLD FACE
HJS6R	JACK,CAT6,UNI,SHIELDED,RED FACE	HJS6AOW	JACK,CAT6A,UNI,SHIELDED,OFF.WHITE FACE
HJS6W	JACK,CAT6,UNI,SHIELDED,WHITE FACE	HJS6AP	JACK,CAT6A,UNI,SHIELDED,PURPLE FACE
HJS6Y	JACK,CAT6,UNI,SHIELDED,YELLOW FACE	HJS6APK	JACK,CAT6A,UNI,SHIELDED,PINK FACE
HJS6AB	JACK,CAT6A,UNI,SHIELDED,BLUE FACE	HJS6BN24	JACK,CAT6,UNI,SHIELDED,BROWN FACE,24PK
HJS6ABK	JACK,CAT6A,UNI,SHIELDED,BLACK FACE	HJS6EI24	JACK,CAT6,UNI,SHIELDED,IVORY FACE,24PK
HJS6AGN	JACK,CAT6A,UNI,SHIELDED,GREEN FACE	HJS6GL24	JACK,CAT6,UNI,SHIELDED,GOLD FACE,24PK
HJS6AGY	JACK,CAT6A,UNI,SHIELDED,GRAY FACE	HJS6OW24	JACK,CAT6,UNI,SHIELDED,OFF.WHITE FACE,24PK
HJS6AOR	JACK,CAT6A,UNI,SHIELDED,ORANGE FACE	HJS6P24	JACK,CAT6,UNI,SHIELDED,PURPLE FACE,24PK
HJS6AR	JACK,CAT6A,UNI,SHIELDED,RED FACE	HJS6PK24	JACK,CAT6,UNI,SHIELDED,PINK FACE,24PK
HJS6AW	JACK,CAT6A,UNI,SHIELDED,WHITE FACE	HJS6ABN24	JACK,CAT6A,UNI,SHIELDED,BROWN FACE,24PK
HJS6AY	JACK,CAT6A,UNI,SHIELDED,YELLOW FACE	HJS6AEI24	JACK,CAT6A,UNI,SHIELDED,IVORY FACE,24PK
HJS6B24	JACK,CAT6,UNI,SHIELDED,BLUE FACE,24PK	HJS6AGL24	JACK,CAT6A,UNI,SHIELDED,GOLD FACE,24PK
HJS6BK24	JACK,CAT6,UNI,SHIELDED,BLACK FACE,24PK	HJS6AOW24	JACK,CAT6A,UNI,SHIELDED,OFF.WHITE FACE,24PK
HJS6GN24	JACK,CAT6,UNI,SHIELDED,GREEN FACE,24PK	HJS6AP24	JACK,CAT6A,UNI,SHIELDED,PURPLE FACE,24PK
HJS6GY24	JACK,CAT6,UNI,SHIELDED,GRAY FACE,24PK	HJS6APK24	JACK,CAT6A,UNI,SHIELDED,PINK FACE,24PK
HJS6OR24	JACK,CAT6,UNI,SHIELDED,ORANGE FACE,24PK		
HJS6R24	JACK,CAT6,UNI,SHIELDED,RED FACE,24PK		
HJS6W24	JACK,CAT6,UNI,SHIELDED,WHITE FACE,24PK		
HJS6Y24	JACK,CAT6,UNI,SHIELDED,YELLOW FACE,24PK		
HJS6AB24	JACK,CAT6A,UNI,SHIELDED,BLUE FACE,24PK		
HJS6ABK24	JACK,CAT6A,UNI,SHIELDED,BLACK FACE,24PK		
HJS6AGN24	JACK,CAT6A,UNI,SHIELDED,GREEN FACE,24PK		
HJS6AGY24	JACK,CAT6A,UNI,SHIELDED,GRAY FACE,24PK		
HJS6AOR24	JACK,CAT6A,UNI,SHIELDED,ORANGE FACE,24PK		
HJS6AR24	JACK,CAT6A,UNI,SHIELDED,RED FACE,24PK		
HJS6AW24	JACK,CAT6A,UNI,SHIELDED,WHITE FACE,24PK		
HJS6AY24	JACK,CAT6A,UNI,SHIELDED,YELLOW FACE,24PK		




OPTIONAL COLORED FACE



NOTES:

- JACKS COMPLY WITH TIA 568.C.2 CATEGORY 6 OR 6A PERFORMANCE.
- IDC TERMINATION ACCEPTS WIRE GAUGE: 22 TO 24 AWG.
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

Created on INVENTOR	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES: .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT REFERENCE: PMR 007-19		 <b>Hubbell Premise Wiring</b> HUBBELL INCORPORATED (Delaware) 23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL:		
	DRAWN BY: D.O'CONNOR 3/5/19		CHECKED BY:		SIZE: <b>C</b> DRAWING NO. <b>HWS14869C</b> REV. <b>2</b>
	APPROVED BY:		SCALE: N/A		SHEET 1 OF 1

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
2	23925	3/9/20	REVISED TABLE	DPO	MMA