


30A 600V A.C. RATINGS	
HP	VOLTAGE
1 HP	120V AC 1Ø
3 HP	200-240V AC 1Ø
5 HP	480V AC 1Ø
7.5 HP	200-240V AC 3Ø
15 HP	480V AC 3Ø
15 HP	600V AC 3Ø



- NOTES UNLESS OTHERWISE SPECIFIED:**
1. CATALOG NUMBER: HBLDS3SSRP.
 2. DIMENSIONS SHOWN ARE IN INCHES [mm].
 3. ENCLOSURE TYPE 4X, 12.
 4. cULus LISTED.
 5. NSF CERTIFIED AND IP69K RATING.

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
ENCLOSURE & HARDWARE	STAINLESS STEEL	
HANDLE & MOUNT	PBT	
GASKET	EPDM FOAM	
LENS	PC	
LED/PCBD		

SYM	DESCRIPTION	APPROVED	DATE
3	REMOVED VIEW OF CONDUIT HUB & VIEW OF HUB WITH DIMENSIONS; REMOVED HUB FROM PARTS LIST DCN 220907023814 RM	JCF	10/3/22
2	CORRECTED ASSEMBLY VIEW. CORRECTED DIMS. FROM 5.30 to 4.88 PER DCN 23241 CAC	TLS	08/01/17
1	RELEASED PER DCN# 22777 CAC TLS	TLS	01/06/17

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE CIRCUIT-LOCK™ 30 AMP SLOPED TOP STAINLESS STEEL DISCONNECT SWITCH LED INDICATORS

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
FRACTIONS	± 1/64	DR. BY	CAC
DECIMALS	± .030	APP. BY	TLS
ANGLES	± 2'	TR. BY	
		SCALE	NONE
		CHK'D BY	TLS
		DATE	1/6/2017

DIMENSION SHEET FOR CAT. NO. HBLDS3SSRP

REPAIRABLE NON-REPAIRABLE

B | **M-13543** | **3**