



NOTES:

1. MATERIALS:  
HOUSING: ALUMINUM  
DECORATOR PLATES: U/L 94 V-0 RATED THERMOPLASTIC
2. INCLUDES MOUNTING HARDWARE AND INSTRUCTIONS
3. REQUIRES ISFHDR4BK DISPLAY RECIEVER.
4. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
2	22542	12/5/17	REVISED LABELING	DPO	MMA
1	22468	7/20/17	INITIAL RELEASE	DPO	MMA

**Created on INVENTOR**

DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES: XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°

IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION

PROJECT REFERENCE:  
NPD-01690

MATERIAL:

DRAWN BY:  
D.O'CONNOR 5/1917

CHECKED BY:

APPROVED BY:

**HUBBELL** Hubbell Premise Wiring  
HUBBELL INCORPORATED (Delaware)  
23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355

TITLE:  
4KAV VGA/HDMI/USB/3.5mm TRANSMITTER

SIZE: **C** DRAWING NO.: **HWS14755C** REV.: **2**

SCALE: SHEET **1** OF **1**