



1. Point Stop
2. Mode LED
3. Sense LED
4. Phase to Phase Scale
5. Phase to Ground Scale
6. LED Legend
7. Audible Alarm
8. Power Button
9. "BAT" Battery Voltage Level Indicator

### Features

- Capacitive test point through 80kV AC for overhead and underground systems
- Power-saving sleep mode (auto-off)
- Equivalent Phase-to-Phase and Phase-to-Ground reading ranges
- Manually activated hold mode
- Bluetooth technology

CATALOG NO.	DESCRIPTION	INCLUDES
PSC4033710	MRVI, 80kV	MRVI w/ Bag
PSC4033925	MRVI, 80kV	MRVI w/o Bag Straight Probe Hard Carrying Case
PSC4033810	MRVI Kit, Overhead and Underground	MRVI w/o Bag Bushing Adapter for up to 35kV Elbow Adapter for up to 35kV Straight Probe Hard Carrying Case

# MULTI-RANGE VOLTAGE INDICATOR (MRVI)



<b>CHANCE</b> <sup>®</sup> <small>CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION, OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.</small>	<b>HUBBELL POWER SYSTEMS, INC.</b>		
	<b>MULTI-RANGE VOLTAGE INDICATOR</b>		
	SIZE <b>B</b>	CAT / PART / ASSY NO. <b>SEE CHART</b>	DWG NO. <b>SA4033710</b>
	DO NOT SCALE THIS DRAWING	DRN BY TLK	DATE 10/29/18
		REV <b>A</b>	
		SHEET 1 OF 1	