



**SHORT CIRCUIT STICK
4 CLAMPS (30cm SPACING)**

**CATALOG NO.
PST6003615**

IEC 61230 RATING: 3kA / 1sec ($\leq 1000V$)

CONDUCTOR RANGE: 3.5mm - 19.5mm

PART NUMBER	ITEM	DESCRIPTION	QTY
P403-1396	1	HANDLE	1
PSP4033770	2	STORM GUARD, 1-1/16"	1
PSP6003558	3	GRIPPER	4
PSZ0012444	4	RIVET, 3/16"	4
PSZ0012447	5	COMPRESSION SPRING	4
P001-0248	6	PIN, 0.187" X 1.312"	4
PSP6003593	7	CHANNEL, 32" LONG	1
PSP4004344	8	POLE, 1-1/16" X 48"	1
PSP6003595	9	POLE CAP, 1-1/16"	1

EPOXIGLAS DIA: 26.99mm
ELECTRICALLY TESTED PER ASTM F711
AND IEC 60855

<p>CHANCE[®]</p> <p><small>CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS</small></p>	<p>HUBBELL[®] HUBBELL POWER SYSTEMS, INC. <small>POWER SYSTEMS, INC.</small></p>			
	<p>TITLE SHORT CIRCUIT STICK, 4 CLAMPS (30 CM SPACING)</p>			
	<p>SIZE C</p>	<p>DWG NO. SAPST6003615</p>	<p>CAT / PART / ASSY NO. PST6003615</p>	
<p>DO NOT SCALE THIS DRAWING</p>		<p>DRN BY BSU</p>	<p>DATE 12/18/18</p>	<p>SHEET 1 OF 1</p>