



REV	DATE	DESCRIPTION	ECO	BY	C.H.K.
D	02/13/2014 00:00:00 AM	DRAWING UPDATE AS PER MARKUP	33954	RK	MB

CONDUCTOR		CAT. NO	B	L	O.D	INDEX NO	INSTALLATION DATA													
COPPER CABLE SIZE	STR						HYPRESS™ DIE SETS WITH NO. OF CRIMPS EACH END													
							MO6		Y35		Y46		Y488		Y60		KEARNEY		NICOPRESS	
#8 SOL (Ø.129)	---	YDS8W	.70	1.65	.25	171	W171	1	U171	1	---	-	---	-	---	-	K 1/4	-	N-E	-
#6 SOL (Ø.162)	---	YDS6W	1.27	2.62	.32	161	W161	2	U161	1	---	-	---	-	---	-	K 5/16	-	N-J	-
#4 SOL (Ø.204)	---	YDS4W	1.15	2.55	.38	162	W162	4	U162	1	---	-	---	-	---	-	K 3/8	-	N-M	-
#3 SOL (Ø.229)	---	YDS3W	1.21	2.75	.48	163/308	W163	4	U163/U308	2	---	-	---	-	---	-	---	-	---	-
#2 SOL (Ø.258) #3 STR (Ø.260)	---	YDS2W	1.75	3.75	.48	163	W163	6	U163	2	---	-	---	-	---	-	K 1/2	-	N-T	-
#1 SOL (Ø.289)	---	YDS1W	2.64	5.53	.55	164	W164	8	U164	4	---	-	---	-	---	-	---	-	---	-
#1/0 SOL (Ø.325)	---	YDS75	2.84	5.93	.61	165/287	W165	6	U165	6	---	-	---	-	---	-	K 5/8-1	-	---	-
3#6 (Ø.349) 2/0 SOL (Ø.365)	---	YDS76	2.97	6.19	.68	166/206	W166 W206	12	U166 U206	6	---	-	---	-	---	-	---	-	---	-
3/0 SOL (Ø.410)	---	YDS77	3.51	7.39	.76	207	---	-	U207	7	---	-	---	-	---	-	---	-	---	-
4/0 SOL (Ø.460)	---	YDS78	3.55	7.47	.86	168	---	-	U168	9	---	-	CI68	3	LI68	3	---	-	---	-



- NOTES:
- U DIES MAY BE USED WITH P-U ADP U DIE ADAPTOR.
 - MATERIAL: COPPER TUBE.
 - BARRELS LINED WITH PENETROX™.

TO ORDER BURNDY® PRODUCTS CALL		HYSPLICE™ TENSION (COPPER)	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: NA	CAT. NO: YDS (TABLE)
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		DRAWN BY: JDI 11-08-71	CHECKER: J.P.S 11-11-71
FOR PRODUCT INFO: http://www.burndy.com		DSN APPVL: --	MFG APPVL: JOE 06/24/13
		QA APPVL: CHARLES 06/20/13	MKT APPVL: HALL 06/20/13
		PROD FAM: --	SCALE: NTS
		PROJECT #: --	DRAWING NO: SD015142
		DOCUMENT TYPE: Sales	REV: D
		REL LEVEL: Released	SHEET 2 OF 3

REV: PEO200