


CATALOG NO.	CONDUCTOR			B	L	O.D.	INSTALLATION DATA OVERLAP CRIMPS EACH END		
	Kcmil AL.	STR.	DIA.				BURNDY HYPRESS™ & DIE SET		T&B DIE SET
							TOOL DIE NO.	Y60	T&B 21940 TYPE PRESS
YTS301A	336.4 350	19 37	.666[17] .681[17]	4.50 [114]	9.13 [232]	1.14 [29]	717	L717	96
YTS311A	397.5 400	19 37	.724[18] .728[18]	4.51 [115]	9.29 [236]	1.27 [32]	719	L719	106
YTS331A	450 477	37 19, 37	.772[20] .792[20] - .795[20]	4.50 [114]	9.27 [235]	1.28 [33]	719	L719	106
YTS351A	500 556.5	37 19, 37	.813[21] .856[22] - .858[22]	5.47 [139]	11.18 [284]	1.41 [36]	720	L720	115
YTS361A	600 636	61 37	.893[23] .918[23]	5.95 [151]	12.14 [308]	1.50 [38]	722	L722	125
YTS39A	715.5 750	37, 61 61	.974[25] - .975[25] .998[25]	6.61 [168]	13.36 [339]	1.61 [41]	724	L724	140
YTS391A	795 800	37, 61 61	1.026[26] - 1.028[26] 1.031[26]	7.84 [199]	15.81 [402]				
YTS431A	874.5 954	37, 61	1.077[27] 1.124[29] - 1.126[29]	8.15 [207]	16.51 [419]	1.80 [46]	725	L725	150
YTS445A	1033.5	37, 61	1.170[29] - 1.172[29]	9.12 [232]	18.51 [470]	1.97 [50]	727	L727	161
	1113	37, 61	1.216 [31]						
YTS451A	1192.5 1272	61	1.258[32] 1.297[33]	9.08 [231]	18.40 [467]	1.97 [50]	727	L727	161
YTS457A	1351.5 1431	61	1.339[34] 1.379[35]	9.91 [252]	19.96 [507]	2.25 [57]	728	L728	189
YTS463A	1590	61	1.454 [37]	10.62 [270]	21.50 [546]	2.25 [57]	728	L728	189
YTS484A	2300	61	1.750 [44]	9.96 [253]	20.19 [513]	2.50 [64]	735	L735	214
YTS48A	2000	169	1.632 [41]	10.69 [272]	21.62 [549]	2.50 [64]	735	L735	212, 214
YTS486A	2500	91	1.824 [46]	12.06 [306]	24.28 [617]	2.60 [66]	740	L740	---
YTS47A	1750	61	1.525 [39]	9.91 [252]	19.96 [507]	2.25 [57]	728	L728	189

REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	05/10/2012	UPDATE SALES DRAWING AS PER MARKUP	27259	DD	MB



NOTES:

- 1 THE EQUIVALENT T & B DIE INDEXES ARE LISTED FOR YOUR CONVENIENCE.
2. INSTALLATION INSTRUCTIONS FORM#3408, DRAWING # 30003108.
3. CONNECTOR IS INDIVIDUALLY PACKAGED & SEALED IN POLYTUBE.
4. MATERIAL: ALUMINUM TUBE.
5. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS, ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED. METRIC DIMENSIONS ARE FOR REFERENCE ONLY.

REFERENCE: SD061865

TO ORDER BURNDY® PRODUCTS CALL		TENSION HYSPLICE™ (ALUM.)	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: H.C. 7/7/1966	
		CHECKER: MJM 9/14/1966	
		DSN APRVL: ARH 9/16/1966	
		MFG APRVL: [blank]	
		QA APRVL: [blank]	
		MKT APRVL: [blank]	
		PROD FAM: [blank]	DRAWING NO
		PROJECT #: [blank]	SD061864-01
		DOCUMENT TYPE: SALES	REV
		REL LEVEL: Released	A
		SIZE: D	SHEET 1 OF 1