


NOTES:

- MATERIAL: ALUMINUM
- WITH GROUND WIRE CLAMP (SUPPLIED STANDARD).
- ULTIMATE LOAD 6,000# TOTAL 2,000# PER POSITION.
- 12" NEMA TRANSFORMER SPACING.
- EE1-NEMA TYPE A LUGS.
- COMPLETELY ASSEMBLED WITH HARDWARE.
- A- BOLT PACK INCLUDED (STANDARD).
- MOUNTS 3KVA THRU 167 KVA TRANSFORMERS
- MOUNTS THREE TRANSFORMERS 6" FROM POLE.

				TO ORDER CMC PRODUCTS		DRAWN BY: TS		NAME OF PART:		CAT. NO.:	
				UNITED STATES 1-513-860-4455		04-22-20		BANDED TRANSFORMER CLUSTER MOUNT		BMAC-3156	
				CANADA 1-800-361-6975		CHECKED BY:		DWG NO:		A	
				MEXICO 011-52-722-265-4400				UB20700158-S			
A NEW DRAWING CREATED				04-22-20		TS		DRAWING NOT TO SCALE		SHEET NO: 1 OF 1	
REV.	DESCRIPTION			ECN	DATE	INIT.					

THIS INFORMATION IS PROPRIETARY TO CONNECTOR MFG. CO. AND IS NOT TO BE DISCLOSED OUTSIDE OF CONNECTOR MFG. CO. WITHOUT A CONFIDENTIALITY AGREEMENT



CONNECTOR MANUFACTURING CO.

HAMILTON, OHIO