


- MOUNTING BOARD IS 3/4" EXTERIOR GRADE TREATED PLYWOOD IN STANDARD.
- STANDARD DOUBLE SWINGING DOORS WITH STAINLESS STEEL LIFT-OFF HINGES, 3-POINT LOCKING HANDLE. DOORS HAVE BRACKETS, WHICH HOLD THEM IN THE OPEN POSITION
- MATERIAL IS ALUMINIUM
- HUBS PROVIDED WHEN REQUESTED AT EXTRA CHARGE
- 4" LOUVERS WITH SCREENS (STANDARD)
- GROUND LUG IS AL-CU LUG FURNISHED (STANDARD)
- NEMA 3R, BOARD SIZE 27" X21"

				TO ORDER CMC PRODUCTS		DRAWN BY: TS		NAME OF PART:		CAT. NO.:	
				UNITED STATES 1-513-860-4455		10-26-20		OUTDOOR METER, INSTRUMENT TRANSFER & SUBSTATION EQUIPMENT ENCLOSURE		BA123036DD	
				CANADA 1-800-361-6975		CHECKED BY:		DWG NO:		A	
				MEXICO 011-52-722-265-4400				UB22700067-S			
A NEW DRAWING CREATED				10-26-20		TS		DRAWING NOT TO SCALE		SHEET NO: 1 OF 1	
REV.	DESCRIPTION			ECN	DATE	INIT.					

THIS INFORMATION IS PROPRIETARY TO CONNECTOR MFG. CO. AND IS NOT TO BE DISCLOSED OUTSIDE OF CONNECTOR MFG. CO. WITHOUT A CONFIDENTIALITY AGREEMENT



CONNECTOR MANUFACTURING CO.

HAMILTON, OHIO