


- MOUNTING BOARD IS 3/4" EXTERIOR GRADE TREATED PLYWOOD IN STANDARD.
- STANDARD DOUBLE SWINGING DOORS WITH STAINLESS STEEL LIFT-OFF HINGES, 3-POINT LOCKING HANDLE. DOORS HAVE BRACKETS, WHICH HOLD THEM IN THE OPEN POSITION
- HUBS PROVIDED WHEN REQUESTED AT EXTRA CHARGE
- 4" LOUVERS WITH SCREENS (STANDARD)
- GROUND LUG IS AL-CU LUG FURNISHED (STANDARD).
- NEMA 3R, BOARD SIZE 29" X 37"
- MATERIAL: ALUMINUM

					TO ORDER CMC PRODUCTS	DRAWN BY: TS 12-21-20	NAME OF PART: OUTDOOR METER, INSTRUMENT TRANSFER & SUBSTATION EQUIPMENT ENCLOSURE	CAT. NO.: BA133240DD
					UNITED STATES 1-513-860-4455	CHECKED BY:	DWG NO: UB22700451-S	A
					CANADA 1-800-361-6975	DRAWING NOT TO SCALE		SHEET NO: 1 OF 1
					MEXICO 011-52-722-265-4400			
A	NEW DRAWING CREATED		12-21-20	TS	FOR PRODUCT INFO www.cmdlugs.com			
REV.	DESCRIPTION	ECN	DATE	INIT.				

THIS INFORMATION IS PROPRIETARY TO CONNECTOR MFG. CO. AND IS NOT TO BE DISCLOSED OUTSIDE OF CONNECTOR MFG. CO. WITHOUT A CONFIDENTIALITY AGREEMENT



CONNECTOR MANUFACTURING CO.

HAMILTON, OHIO