




M-13176

1



SECTION A-A
THROUGH FLOOR BOX

NOTES:
1. PRODUCT IS UL & CSA LISTED.COMPLIES WITH UL 514A, CSA C22.2 NO. 85-14.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
FLOOR BOX (2-GANG)	GRAY IRON	GRAY
ADJUSTING BASE	STEEL	ZINC PLATE
BOX DIVIDER	STEEL	ZINC PLATE
ADJUSTABLE COLLAR	GRAY IRON	GRAY
COVER FRAME ASSY	BRASS/AL	
SCREW,LEVELING	STEEL	ZINC PLATE
SCREW FLAT HEAD	STEEL	ZINC PLATE
SCREW ROUND HEAD	STEEL	ZINC PLATE
GROUNDING SCREW & PIGTAIL	COPPER	GREEN INSUL
CONCRETE COVER	TIN	TIN PLATE

DIMENSION SHEET FOR CAT. NO. B2432, BA2432

1	INITIAL RELEASE. PER DCN 22067	DDL	04/18/16
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE
STAMPED STEEL, RECTANGULAR, TWO GANG, 3.75" DEEP FAMILY




WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT


TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2'	DR. BY	SCALE	NONE
	CHK. BY DDL	DATE	04/15/16

M-13176


1




B2432
BA2432
STAMPED STEEL FLOOR BOX




S3825
SA3825




S3625
SA3625




S3826
SA3826




S2425
SA2425



S2625
SA2625



S2825
-



S3813
SA3813

SHOWN SINGLE SERVICE COVERS SOLD SEPARATELY

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
SEE SHEET 1		

DIMENSION SHEET FOR CAT. NO.
B2432, BA2432

1	INITIAL RELEASE. PER DCN 22067	DDL	04/18/16
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE
STAMPED STEEL, RECTANGULAR, TWO GANG, 3.75" DEEP FAMILY



WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2'	DR. BY	SCALE	NONE
	CHK. BY	DATE	04/15/16

SHEET 2 OF 2

B
M-13176
1